


SM6404

Magnetic-inductive flow meter

SMK12GGX50KG/US-100



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 2	
Process connection	threaded connection Rc 1/2 internal thread DN15	
Temperature monitoring		
Measuring range	[°C]	-20...80

Application

Special feature	Gold-plated contacts	
Application	for industrial applications	
Media	conductive liquids; water; hydrous media	
Note on media	conductivity: $\geq 20 \mu\text{S}/\text{cm}$ viscosity: $< 70 \text{ mm}^2/\text{s}$ (40 °C)	
Medium temperature	[°C]	-10...70
Pressure rating	[bar]	16

Electrical data

Operating voltage	[V]	20...30 DC; (according to EN 50178 SELV/PELV)
Current consumption	[mA]	120; (24 V)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	5

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 2
------------------------------	-------------------------------

SM6404



Magnetic-inductive flow meter

SMK12GGX50KG/US-100

Outputs		
Total number of outputs		2
Output signal		analogue signal
Number of analogue outputs		2
Analogue current output [mA]		4...20; (scalable)
Max. load [Ω]		500
Overload protection		yes
Measuring/setting range		
Measuring range		0.1...25 l/min
Display range		-30...30 l/min
Resolution		0.05 l/min
Analogue start point ASP		0...20 l/min
Analogue end point AEP		5...25 l/min
In steps of		0.05 l/min
Temperature monitoring		
Measuring range [°C]		-20...80
Resolution [°C]		0.2
Analogue start point [°C]		-20...60
Analogue end point [°C]		0...80
In steps of [°C]		0.2
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		± (0,8 % MW + 0,5 % MEW)
Repeatability		± 0,2% MEW
Temperature monitoring		
Accuracy [K]		± 2,5 (Q > 1 l/min)
Response times		
Flow monitoring		
Response time [s]		0.15; (dAP = 0, T19)
Damping for the switching output dAP [s]		0...3
Temperature monitoring		
Dynamic response T05 / T09 [s]		T09 = 20 (Q > 1 l/min)
Operating conditions		
Ambient temperature [°C]		-10...60
Storage temperature [°C]		-25...80
Protection		IP 67

SM6404



Magnetic-inductive flow meter

SMK12GGX50KG/US-100


Tests / approvals				
EMC	DIN EN 60947-5-9	500 V withstand voltage (V DC)		
Shock resistance	DIN IEC 68-2-27	20 g (11 ms)		
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000 Hz)		
MTTF [years]		175		
UL approval	UL Approval no.	I011		
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request			
Mechanical data				
Weight [g]		555		
Materials	stainless steel (1.4404 / 316L); PBT-GF20; PC; FKM; TPE			
Materials (wetted parts)	stainless steel (1.4404 / 316L); PEEK; FKM			
Process connection	threaded connection Rc 1/2 internal thread DN15			
Displays / operating elements				
Display	Display unit measured values programming	6 x LED, green (l/min, m³/h, gpm, gph, °C, °F) alphanumeric display, 4-digit alphanumeric display, 4-digit		
Remarks				
Remarks	MW = measured value MEW = Final value of the measuring range			
Pack quantity	1 pcs.			
Electrical connection				
Connector: 1 x M12; Contacts: gold-plated				



Magnetic-inductive flow meter

SMK12GGX50KG/US-100

Connection



colours to DIN EN 60947-5-2

OUT1: analogue output Temperature monitoring

OUT2: analogue output volumetric flow quantity monitoring

Core colours :

BK = black


BN = brown

BU = blue

WH = white

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity