

NOT RECOMMENDED

NM232DDC Series

FOR NEW DESIGNS



ELECTRICAL CHARACTERISTIC	CS				
Parameter	Test conditions	Min	Тур.	Max.	Units
High threshold input logic, V _{IH}	TX _{IN} , SHUTDOWN, ENABLE		1.8	2.4	V
Low threshold input logic, V _L	TX _{IN} , SHUTDOWN, ENABLE	0.8	1.3		V
Input Hysteresis, ΔVτ	TXin		0.5		V
Leakage Current, I∟	TX_{IN} , SHUTDOWN or $\overline{ENABLE} = V_{CC}$			10	μA
Input capacitance, C _{IN}	TXin		5.0		pF
Low level output voltage, Vol	Ιουτ = 3.2mA			0.4	V
High level output voltage, Vон	lо∪т = -1.0mA	2.4			V
Input pull up current	$V_{IN} = OV$		4.0	20	μA
±VREF Current	T Xου $\tau = 3$ k Ω , R Xου $\tau = 2.2$ k Ω			3.0	mA

ATURES	ELECTRICAL CHARACTERISTICS - EIA-232-D					
oHS compliant	Parameter	Test conditions	Min	Тур.	Max.	Units
ingle 5V supply	Positive going threshold, V _{T+}	RXIN		1.8	3.0	V
ingle 5v Supply	Negative going threshold, V _{T-}	RXIN	0.6	1.2		V
0μW low power shutdown	Input Hysteresis, ΔVτ	RXIN		0.6		V
TL/CMOS Logic compatible	Input resistance	RXIN	3.0		7.0	kΩ
	Output voltage, VPP	TXουτ, RL=3kΩ to ISO GND	±5.0	±7.0		V
IA-232-D/E and CCITT V.28 compatible	Output leakage current, I∟	SHUTDOWN=Vcc, TXouT=±15V	-10		10	μА
ual transmitters and receivers	Output slew rate, S _R	$R_L=3k\Omega$, $C_L=2500pF$		3.0	30	V/µs
	Propagation delay, TL	Logic to RS232		20		μs
.5kVrms Isolation	Propagation delay, T _R	RS232 to logic		10		μs
	Transmission rate	RL= $3k\Omega$, CL= $2500pF$			9.6	kbps
SCRIPTION	Supply voltage, Vcc		4.5		5.5	V
NM232DDC is an electrically isolated dual smitter and receiver designed to inter-	Supply current, Icc	TXIN=0.8V, TXOUT= $3k\Omega$, RXIN= $3.0V$, RXOUT= $2.2k\Omega$		53		mA
data terminal equipment (DTE) with data	Shutdown current Icc	SHUTDOWN=1		1.0	10	μA
munications equipment (DCE). The device	ENABLE input current, IEN	ENABLE=0V to Vcc			1.0	μΑ
ides two data receive channels and two data	Shutdown input current, Ізнитроми	SHUTDOWN=OV to Vcc			1.0	μА
smit channels. Each channel is EIA-232-D,	MTTF ¹		187			kHrs

TEMPERATURE CHARACTERISTICS				
Parameter	Min	Тур.	Max.	Units
Operating free-air temperature range	0		70	°C
Storage temperature range	-55		125	°C

ABSOLUTE MAXIMUM RATINGS		
Supply voltage Vcc with respect to pin 10		-0.3V to +6V
Input voltage to logic pins 3, 7, 8, & 11 with respect to pin 10		-0.3V to Vcc+0.3V
	EIA-232-D input voltage, pins 17 & 18	-30V to +30V
Voltages with respect to ISO GND pin 22	EIA-232-D input voltage, pins 19 & 20	-15V to +15V
	Positive input voltage, pins 16 & 21	+14V
	Negative input voltage, pin 23	-14V
Short circuit on pins 19 & 20		Indefinite
Power dissipation		700mW
NM232DDC maximum data rate		9.6kbps
Lead case temperature 1.5mm from case for 10 seconds		300°C

ISOLATION CHARACTERISTICS					
Parameter	Conditions	Min	Тур.	Max.	Units
Isolation test voltage	Flash tested for 1 second	1500			Vrms

^{1.} Calulated using MIL-HDBK-217F. All data taken at T_A=25°C, V_{CC}=5V.

FEAT

RoHS	compliant
------	-----------

Sir

50

■ TT

EIA

Du

1.5

DES(

The N transn face d comm provid transmit channels. Each channel is EIA-232-D, EIA-232-E and CCITT V.28 compatible at the interface boundary and TTL/CMOS compatible at the logic connections. No external components are needed and a single 5V input supply powers all functions either side of the isolation boundary. A low-power shutdown mode and high impedance state for receiver outputs is effected via two pins, SHUTDOWN and ENABLE. The device is supplied in a low profile 24 pin DIL package.





Isolated Dual EIA-232-D Transmitter and Receiver

APPLICATION NOTES

The NM232DDC is an isolated interface device providing EIA-232-D compatibility. A single supply from the logic side provides all necessary power for the device. The isolation feature allows the protective or frame ground of DTEs or DCEs to be isolated from each other, eliminating ground loop currents and inherently long noise paths. The voltage level between different ground points can be up to $\pm 5 \text{V}$ or $\pm 6 \text{V}$ and this level flucuates as the power taken varies. This voltage appears, in non-isolated equipment, as normal mode noise on the signals. With such high noise levels present it is clearly very difficult with single ended signals to have reliable communication. Isolating the input from output so that one side floats relative to the other allows reliable communication in environments with considerable degrees of noise between equipments.

Figure 1 shows a typical pcb track layout with a clear separation between the logic pin connections (pins 1-12) and the EIA-232-D connections (pins 13-24). Between the two sides of the layout is a track which can be connected to frame or equipment ground, this can be seen as the boundary between the logic and EIA-232-D side of the device. No other rules or speed conditions need to be applied other than to keep the two halves' separation to a maximum.


An example of a DTE application circuit is shown in figure 2. The schematic is illustrative of the way the NM232DDC may be connected to implement an isolated EIA-232-D interface with a typical UART and processor bus. Precise circuitry will depend on the application and in particular the use of the control lines shown will need to be altered to suit the situation.

The ENABLE control line (pin 11), puts the receiver output pins 1 and 12 into a high impedance state when set to a high level. The shutdown control line (pin 3) sets the device into a shutdown power mode when it is at high logic level. The maximum power drawn in shutdown mode is 50µW, a low enough level for consideration in battery powered equipment.

Where to use the NM232DDC

The function of the NM232DDC is to provide an isolated signal path between a UART or similar device and the EIA-232-D interface 'D' connector, providing two receivers and two transmitters which can be used in a number of handshake modes. One receiver and transmitter will normally be used for the signal lines and the remaining pair will act as handshake lines. Figure 3 shows simply where the device will be connected.

More complicated schemes for controlled signal interchange will require two or more such devices. As the devices are self contained no external DC/DC converter is required. The enable line provides a means for creating a communications bus where each NM232DDC can have a different logical address via a decoder. This would allow one UART to talk with many EIA-232-D connected interfaces (see figure 4).



ROHS COMPLIANCE INFORMATION





This series is compatible with RoHS soldering systems with a peak wave solder temperature of 300°C for 10 seconds. The pin termination finish on this product series is Matte Tin over Nickel Preplate. The series is backward compatible with Sn/Pb soldering systems.


For further information, please visit www.murata-ps.com/rohs


Isolated Dual EIA-232-D Transmitter and Receiver


TYPICAL OPERATING CHARACTERISTICS

















Isolated Dual EIA-232-D Transmitter and Receiver



PIN (PIN CONNECTIONS				
Pin	Function	Description			
1	R1 оит	Receiver output number 1, TTL/CMOS logic			
2	NC	No internal connection			
3	SHUTDOWN	SHUTDOWN input, High=SHUTDOWN, Low=normal operation			
4	NC	No internal connection			
5	Vcc	+5V supply			
6	NC	No internal connection			
7	T2 _{IN}	Transmitter input number 2, TTL/CMOS logic			
8	T1 _{IN}	Transmitter input number 1, TTL/CMOS logic			
9	NC	No internal connection			
10	GND	Ground			
11	ENABLE	Output ENABLE, High-Hi Z on R1/R2out, low-normal operation			
12	R2оит	Receiver output number 2, TTL/CMOS logic			
13	NC	No internal connection			
14	NC	No internal connection			
15	NC	No internal connection			
16	+V _{REF}	Isolated+V supply out internally connected to pin 21			
17	R2IN	Receiver input number 2, RS232 levels			
18	R1 _{IN}	Receiver input number 1, RS232 levels			
19	Т2оит	Transmitter output number 2, RS232 levels			
20	Т1 оит	Transmitter output number 1, RS232 levels			
21	+V _{REF}	Isolated +V supply out internally connected to pin 16			
22	ISO GND	Isolated ground			
23	-V _{REF}	Isolated +V supply out-			
24	NC	No internal connection			







Isolated Dual EIA-232-D Transmitter and Receiver

TECHNICAL NOTES

ISOLATION VOLTAGE

'Hi Pot Test', 'Flash Tested', 'Withstand Voltage', 'Proof Voltage', 'Dielectric Withstand Voltage' & 'Isolation Test Voltage' are all terms that relate to the same thing, a test voltage, applied for a specified time, across a component designed to provide electrical isolation, to verify the integrity of that isolation.

Murata Power Solutions NM232DDC series of DC/DC converters are all 100% production tested at their stated isolation voltage. This is 1.5kVrms for 1 second.

A question commonly asked is, "What is the continuous voltage that can be applied across the part in normal operation?"

For a part holding no specific agency approvals, such as the NM232DDC series, both input and output should normally be maintained within SELV limits i.e. less than 42.4V peak, or 60VDC. The isolation test voltage represents a measure of immunity to transient voltages and the part should never be used as an element of a safety isolation system. The part could be expected to function correctly with several hundred volts offset applied continuously across the isolation barrier; but then the circuitry on both sides of the barrier must be regarded as operating at an unsafe voltage and further isolation/insulation systems must form a barrier between these circuits and any user-accessible circuitry according to safety standard requirements.

REPEATED HIGH-VOLTAGE ISOLATION TESTING

It is well known that repeated high-voltage isolation testing of a barrier component can actually degrade isolation capability, to a lesser or greater degree depending on materials, construction and environment. The NM232DDC series has toroidal isolation transformers, with no additional insulation between primary and secondary windings of enameled wire. While parts can be expected to withstand several times the stated test voltage, the isolation capability does depend on the wire insulation. Any material, including this enamel (typically polyurethane) is susceptible to eventual chemical degradation when subject to very high applied voltages thus implying that the number of tests should be strictly limited. We therefore strongly advise against repeated high voltage isolation testing, but if it is absolutely required, that the voltage be reduced by 20% from specified test voltage.

Murata Power Solutions, Inc.
11 Cabot Boulevard, Mansfield, MA 02048-1151 U.S.A.
ISO 9001 and 14001 REGISTERED



This product is subject to the following <u>operating requirements</u> and the <u>Life and Safety Critical Application Sales Policy</u>:

Refer to: http://www.murata-ps.com/requirements/

Murata Power Solutions, Inc. makes no representation that the use of its products in the circuits described herein, or the use of other technical Information contained herein, will not infringe upon existing or future patent rights. The descriptions contained herein do not influe granting of licenses to make, use, or sell equipment constructed in accordance therewith. Specifications are subject to change without notice.