

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 02.06.2017

Version number 6

Revision: 02.06.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name: UHU twist & glue Colle Multi-Matériaux**
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Adhesives
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
UHU GmbH & Co.KG
Herrmannstraße 7
D-77815 Bühl (Baden)
Tel.: 0049-(0)7223-284-0
email: info@uhu.boltongroup.de
- Fax: 0049-(0)7223-284-245
- **Further information obtainable from:** UHU QESH
- **1.4 Emergency telephone number:**
Tel.: + 49 (0) 30/19240 (Notruf)
Tel.: + 49 (0) 72 23/28 40

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Liq. 2 H225 Highly flammable liquid and vapour.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS02

- **Signal word** Danger
- **Hazard statements**
H225 Highly flammable liquid and vapour.
- **Precautionary statements**
P102 Keep out of reach of children.
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P501 Dispose of contents/container in accordance with local/regional/national/international regulations.
- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 02.06.2017

Version number 6

Revision: 02.06.2017

Trade name: UHU twist & glue Colle Multi-Matériaux

 · **vPvB:** Not applicable.

(Contd. of page 1)

SECTION 3: Composition/information on ingredients

 · **3.2 Mixtures**

 · **Description:** Adhesive

 · **Dangerous components:**

CAS: 64-17-5 EINECS: 200-578-6 Reg.nr.: 01-2119457610-43	ethanol ⚠ Flam. Liq. 2, H225	25-50%
CAS: 141-78-6 EINECS: 205-500-4 Reg.nr.: 01-2119475103-46-XXXX	ethyl acetate ⚠ Flam. Liq. 2, H225; ⚠ Eye Irrit. 2, H319; STOT SE 3, H336	2.5-10%
CAS: 67-64-1 EINECS: 200-662-2 Reg.nr.: 01-2119471330-49-XXXX	acetone ⚠ Flam. Liq. 2, H225; ⚠ Eye Irrit. 2, H319; STOT SE 3, H336	2.5-10%

 · **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

 · **4.1 Description of first aid measures**

 · **General information:** Immediately remove any clothing soiled by the product.

 · **After inhalation:** Supply fresh air; consult doctor in case of complaints.

 · **After skin contact:** Immediately wash with water and soap and rinse thoroughly.

 · **After eye contact:**

Rinse opened eye for several minutes under running water. Then consult a doctor.

 · **After swallowing:** Do not induce vomiting; call for medical help immediately.

 · **4.2 Most important symptoms and effects, both acute and delayed**

No further relevant information available.

 · **4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

SECTION 5: Firefighting measures

 · **5.1 Extinguishing media**

 · **Suitable extinguishing agents:**

 CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

 · **For safety reasons unsuitable extinguishing agents:** Water with full jet

 · **5.2 Special hazards arising from the substance or mixture**

No further relevant information available.

 · **5.3 Advice for firefighters**

 · **Protective equipment:** No special measures required.

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 02.06.2017

Version number 6

Revision: 02.06.2017

Trade name: UHU twist & glue Colle Multi-Matériaux

(Contd. of page 2)

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Ensure adequate ventilation
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Send for recovery or disposal in suitable receptacles.
Ensure adequate ventilation.
Pick up mechanically.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** No special precautions are necessary if used correctly.
- **Information about fire - and explosion protection:**
Keep ignition sources away - Do not smoke.
Protect against electrostatic charges.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**
Keep container tightly sealed.
Store in cool, dry conditions in well sealed receptacles.
- **Storage class:** 3
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

64-17-5 ethanol	
WEL	Long-term value: 1920 mg/m ³ , 1000 ppm
141-78-6 ethyl acetate	
WEL	Short-term value: 400 ppm Long-term value: 200 ppm
67-64-1 acetone	
WEL	Short-term value: 3620 mg/m ³ , 1500 ppm Long-term value: 1210 mg/m ³ , 500 ppm

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 02.06.2017

Version number 6

Revision: 02.06.2017

Trade name: UHU twist & glue Colle Multi-Matériaux

(Contd. of page 3)

· DNELs
64-17-5 ethanol

Oral	Verbraucher, Verschlucken Langzeitige Exposition	87 mg/kg bw/day (.)
Dermal	Verbraucher, Hautkontakt Langzeitige Exposition	206 mg/kg bw/day (.)
Inhalative	Verbraucher, Akute Wirkungen, Einatmen	950 mg/m ³ (.)
	Verbraucher, Einatmen Langzeitige Exposition	114 mg/m ³ (.)

141-78-6 ethyl acetate

Oral	Verbraucher, Chronische Wirkungen, Verschlucken	4.5 mg/kg ()
Dermal	Verbraucher, Chronische Wirkungen, Hautkontakt	37 mg/kg ()
Inhalative	Verbraucher, Akute Wirkungen, Einatmen	734 mg/m ³ ()
	Verbraucher, Chronische Wirkungen, Einatmen	367 mg/m ³ ()

67-64-1 acetone

Oral	Verbraucher, Verschlucken Langzeitige Exposition	62 mg/kg bw/day
Dermal	Verbraucher, Hautkontakt Langzeitige Exposition	62 mg/kg bw/day
Inhalative	Verbraucher, Einatmen Langzeitige Exposition	200 mg/m ³

· PNECs
64-17-5 ethanol

Süßwasser	0.96 mg/l (.)
Meerwasser	0.79 mg/l (.)

141-78-6 ethyl acetate

Süßwasser	0.24 mg/l ()
Meerwasser	0.024 mg/l ()
Boden	0.148 mg/kg ()

67-64-1 acetone

Süßwasser	10.6 mg/l
Meerwasser	1.06 mg/l
Boden	29.5 mg/kg

· **Additional information:** The lists valid during the making were used as basis.

· 8.2 Exposure controls
· Personal protective equipment:
· General protective and hygienic measures:

The usual precautionary measures are to be adhered to when handling chemicals.
Avoid direct contact with the chemical/ the product/ the preparation by organisational measures.

· **Respiratory protection:** Not required.

· Protection of hands:

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

(Contd. on page 5)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 02.06.2017

Version number 6

Revision: 02.06.2017

Trade name: UHU twist & glue Colle Multi-Matériaux

(Contd. of page 4)

- **Penetration time of glove material**
The exact break trough time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Not required.

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

Form:	Fluid
Colour:	Colourless
· Odour:	Characteristic
· Odour threshold:	Not determined.

· pH-value: Not determined.

· Change in condition

Melting point/freezing point:	Undetermined.
Initial boiling point and boiling range:	55 °C

· Flash point: -19 °C

· Flammability (solid, gas): Not applicable.

· Ignition temperature: 425 °C

· Decomposition temperature: Not determined.

· Auto-ignition temperature: Product is not selfigniting.

· Explosive properties: Product is not explosive. However, formation of explosive air/vapour mixtures are possible.

· Explosion limits:

Lower:	3.5 Vol %
Upper:	15.0 Vol %

· Vapour pressure at 20 °C: 59 hPa

· Density at 20 °C:	0.945 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not determined.

· Solubility in / Miscibility with water:

Not miscible or difficult to mix.

· Partition coefficient: n-octanol/water: Not determined.

· Viscosity:

Dynamic at 20 °C:	1400 mPas
Kinematic:	Not determined.

· Solvent content:

Organic solvents: 58.7 %

(Contd. on page 6)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 02.06.2017

Version number 6

Revision: 02.06.2017

Trade name: UHU twist & glue Colle Multi-Matériaux

(Contd. of page 5)

Water:	8.0 %
VOC (EC)	58.69 %

Solids content:	33.4 %
------------------------	--------

· 9.2 Other information

All relevant physical data were determined for the mixture. All non determined data are not measurably or not relevant for the characterization of the mixture.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· LD/LC50 values relevant for classification:
64-17-5 ethanol

Oral	LD50	7060 mg/kg (rat)
------	------	------------------

Inhalative	LC50/4 h	20000 mg/l (rat)
------------	----------	------------------

141-78-6 ethyl acetate

Oral	LD50	5620 mg/kg (rabbit)
------	------	---------------------

Inhalative	LC50/4 h	1600 mg/l (rat)
------------	----------	-----------------

67-64-1 acetone

Oral	LD50	5800 mg/kg (rat)
------	------	------------------

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

GB-EN

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 02.06.2017

Version number 6

Revision: 02.06.2017

Trade name: UHU twist & glue Colle Multi-Matériaux

(Contd. of page 6)

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow product to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
Disposal must be made according to official regulations.

· **European waste catalogue**

08 04 09*	waste adhesives and sealants containing organic solvents or other hazardous substances
-----------	--

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

- **14.1 UN-Number**
- **ADR, IMDG, IATA** UN1133
- **14.2 UN proper shipping name**
- **ADR** 1133 ADHESIVES
- **IMDG, IATA** 1133 KLEBSTOFFE, Sondervorschrift 640H
ADHESIVES

- **14.3 Transport hazard class(es)**
- **ADR, IMDG, IATA**



- **Class** 3 Flammable liquids.

(Contd. on page 8)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 02.06.2017

Version number 6

Revision: 02.06.2017

Trade name: UHU twist & glue Colle Multi-Matériaux

(Contd. of page 7)

· Label	3
· 14.4 Packing group · ADR, IMDG, IATA	III
· 14.5 Environmental hazards: · Marine pollutant:	No
· 14.6 Special precautions for user · Danger code (Kemler): · EMS Number: · Stowage Category	Warning: Flammable liquids. - F-E,S-D A
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
· Transport/Additional information:	
· ADR · Limited quantities (LQ) · Excepted quantities (EQ)	5L Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· Transport category · Tunnel restriction code	3 E
· IMDG · Limited quantities (LQ) · Excepted quantities (EQ)	5L Code: E1 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 1000 ml
· UN "Model Regulation":	UN 1133 ADHESIVES, 3, III

SECTION 15: Regulatory information

- 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture
 - Directive 2012/18/EU
 - Named dangerous substances - ANNEX I None of the ingredients is listed.
 - Seveso category P5c FLAMMABLE LIQUIDS
 - Qualifying quantity (tonnes) for the application of lower-tier requirements 5,000 t
 - Qualifying quantity (tonnes) for the application of upper-tier requirements 50,000 t
 - REGULATION (EC) No 1907/2006 ANNEX XVII Conditions of restriction: 3
- 15.2 Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

GB-EN

(Contd. on page 9)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 02.06.2017

Version number 6

Revision: 02.06.2017

Trade name: UHU twist & glue Colle Multi-Matériaux

(Contd. of page 8)

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H225 Highly flammable liquid and vapour.

H319 Causes serious eye irritation.

H336 May cause drowsiness or dizziness.

· Department issuing SDS: UHU QESH**· Contact:**

Frau A. Liar,

Herr Dr. C. Hanf

· Abbreviations and acronyms:

Flam. Liq. 2: Flammable liquids – Category 2

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

· * Data compared to the previous version altered.

GB-EN