# Surface Mount Rectifier





#### Features:

- Optimized for Lan Protection Applications
- Low Profile Package With Built-In Strain Relief For Surface Mounted Applications
- Low Incremental Surge Resistance, Excellent Clamping Capability
- 400W Peak Pulse Power Capability With A 10/1,000Ms Wave Form, Repetition Rate (Duty Cycle): 0.01% (300W Above 78V)
- · Very Fast Response Time
- High Temperature Soldering Guaranteed : 260°C/10 seconds at Terminals

### **Mechanical Data**

· Case: JEDEC SMA molded plastic over passivated chip

Terminals: Solder plated, solderable per MIL-STD-750, method 2026

· Polarity: Colour band denotes cathode end

• Weight: 0.002oz, 0.064g

### **Maximum Ratings and Thermal Characteristics**

Ratings at 25°C ambient temperature unless otherwise specified

Characteristic	Symbol	S1A- 13-F	S1B- 13-F	S1D- 13-F	S1G- 13-F	S1J- 13-F	S1K- 13-F	S1M- 13-F	Units
Maximum repetitive peak reverse voltage	VRRM	50	100	200	400	600	800	1,000	V
Maximum RMS voltage	VRMS	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V DC	50	100	200	400	600	800	1,000	V
Maximum average forward rectified current at T∟=110°C	lf(AV)	1			А				
Peak forward surge current @ TL = 110°C 8.3ms single half-sine-wave superimposed on rated load(JEDEC Method)	Ігѕм	30			А				
Maximum instantaneous forward voltage at 1A	VF	1.1			V				
Maximum DC reverse current T <sub>A</sub> =25°C at rated DC blocking voltage T <sub>A</sub> =125°C	lr	1.05			μА				
Typical junction capacitance (Note 1)	Сл	12			рF				
Typical thermal resistance (Note 2)	RөJA	50			°C/W				
Operating junction and storage temperature range	TJ, TSTG	-55 to +175			°C				

#### Note:

- (1) Measured at 1MHz and applied reverse voltage of 4V
- (2) Thermal resistance from junction to ambient and junction to lead PCB mounted on 0.27" × 0.27" (7 × 7mm²) copper pad areas


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



# Surface Mount Rectifier multicomp PRO


#### FIG.1 - FORWARD DERATING CURVE

AVERAGE FORWARD CURRENT, AMPERES



#### FIG.2 PEAK FORWARD SURGE CURRENT

PEAK FORWARD SURGE **CURRENT, AMPERES** 



NUMBER OF CYCLES AT 60Hz

#### FIG.3 -- TYPICAL FORWARD CHARACTERISTICS

INSTANTANEOUS FORWARD CURRENT, AMPERES





FIG.4 -- TYPICAL REVERSE CHARACTERISTICS


INSTANTANEOUS REVERSE CURRENT MICROAMPERES




PERCENT OF RATED PEAK REVERSE VOLTAGE, %

# FIG.5-TYPICAL JUNCTION CAPACITANCE

JUNCTION CAPACITANCE pF



#### FIG.6-TRANSIENT THERMAL IMPEDANCE



PULSE DURATON, SEC


Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



# Surface Mount Rectifier multicomp PRO




# **Package Outline Dimensions**



DO-214AC(SMA)					
Dim.	Min.	Max.			
А	4.25	4.65			
В	2.4	2.8			
С	1.85	2.15			
D	4.85	5.35			
E	0.2 Typ.				
F	0.9	1.5			
G	0.2 Max.				
Н	1.9	2.3			
I	1.35	1.65			

Dimensions: Millimetres

# **Soldering Footprint**



**Dimensions: Millimetres** 

## **Package Information**

Device	Package	Shipping		
S1A-13-F S1B-13-F S1D-13-F S1G-13-F S1J-13-F S1K-13-F S1M-13-F	DO-214AC (SMA)	5,000 / Tape & Reel		

### **Part Number Table**

Description	Part Number		
	S1A-13-F		
	S1B-13-F		
	S1D-13-F		
Surface Mount Rectifier	S1G-13-F		
	S1J-13-F		
	S1K-13-F		
	S1M-13-F		

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

