

Micrometer heads

Standard size

Mitutoyo

Application:

For installation in measuring instruments and presetters, as a setting and control element on machine tools, for fine adjustment of cross tables



Execution:

- With regular gradation
- With simple clamping shank
- Rotating spindle

Art. no.	32017 028
Brand	MITUTOYO
Manufacturer Part Number	150-192
Display	Nonius
Min./max. length measuring range	0-25 mm
Scale value	0.01 mm
Measuring surface diameter	6.35 mm
Measuring arrangement	Flat
Clamp in shank diameter	10 mm
Clamping shank length	15 mm
Coupling design	Slide coupling
Measuring spindle increments	0.5 mm
Spindle clamping	No
Design	Metric
Calibration Group	DE
Gross Weight	0.123 kg
Product Group	3MA

EAN

4946368021898