

PAR 64 Mains Voltage

PAR 64 CP87 240V 500W NSP

9061147



Range Features

- Pressed glass reflector lamps
- Extremely powerful beam
- Halogen inner capsule, for 100% lumen maintenance through life
- Beam patterns: from very narrow spot through wide angle floods
- Consistency from lamp to lamp
- Instant replaceability without the need to re-focus and re-aim fixtures
- Double internal fused for end of life safety
- Applications
- Theatre lighting
- TV and studio
- Entertainment and Architectural applications
- Displays
- Museums
- Churches
- Towers
- Exhibitions
- Gardens
- Discos



PRODUCT OVERVIEW

Beam angle(°)	Narrow Spot
Colour temperature (K)	3200
EAN code	5410288611471
Type	PAR 64
Watt (Nominal) (W)	500
Ordering number	9061147
Average life (Rated) (h)	300

DATA TABLE

Optical data

Beam angle(°)	Narrow Spot
Colour temperature (K)	3200
Peak intensity (cd)	140000

General data

Burning position	Any
EAN code	5410288611471
Type	PAR 64
Ordering number	9061147

PAR 64 Mains Voltage

PAR 64 CP87 240V 500W NSP
9061147

Range features	<p>Pressed glass reflector lamps Extremely powerful beam Halogen inner capsule, for 100% lumen maintenance through life Beam patterns: from very narrow spot through wide angle floods Consistency from lamp to lamp Instant replaceability without the need to re-focus and re-aim fixtures Double internal fused for end of life safety</p> <p>Applications</p> <ul style="list-style-type: none"> Theatre lighting TV and studio Entertainment and Architectural applications Displays Museums Churches Towers Exhibitions Gardens Discos
Product name	PAR 64 CP87 240V 500W NSP
Average life (Rated) (h)	300
Sales pack quantity	6
Electrical data	
Watt (Nominal) (W)	500
Physical data	
Single packaging type	Box/Sleeve
Weight (kg)	0.74

TECHNICAL DRAWINGS

