

Product characteristics

Inductive sensor

Plastic thread M18 x 1

Cable

Sensing range 8 mm; [nf] non-flush mountable

Electrical data

Electrical design

DC PNP/NPN

Operating voltage [V]

10...36 DC

Protection class

II

Reverse polarity protection

yes

Outputs

Output function

normally open

Voltage drop [V]

< 4.6

Minimum load current [mA]

4

Leakage current [mA]

< 0.8

Current rating [mA]

150

Short-circuit protection

pulsed

Overload protection

yes

Switching frequency [Hz]

320

Range

Sensing range [mm]

8

Real sensing range (Sr) [mm]

8 ± 10 %

Operating distance [mm]

0...6.5

Accuracy / deviations

Correction factors

mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.4 / Al approx. 0.3 / Cu approx. 0.2

Hysteresis [% of Sr]

1...15

Switch-point drift [% of Sr]

-10...10

Environment

Ambient temperature [°C]

-25...80

Protection

IP 67

Tests / approvals

EMC

EN 60947-5-2

MTTF [Years]

2583

Mechanical data

Mounting

non-flush mountable

Housing materials

PBT

Weight [kg]

0.12

Displays / operating elements

Output status indication LED

yellow

Electrical connection


Connection

PVC cable / 2 m; 2 x 0.5 mm²

Wiring

IG5714 - Inductive sensor - eclass: 27270101 / 27-27-01-01

Core colours
BK black



Accessories

Accessories (included)

2 lock nuts

Remarks

Pack quantity

[piece]

1

ifm electronic gmbh • Friedrichstraße 1 • 45128 Essen — We reserve the right to make technical alterations without prior notice. — GB — IG5714 — 08.05.2012