



Part no.: 50114363
TKS 40x60.UV.HT
Reflector

Figure can vary

Contents

- Technical data

Part no.: 50114363 – TKS 40x60.UV.HT – Reflector

Technical data

Mechanical data	
Design	Rectangular
Mounting dimension, width	41 mm
Reflection surface width	37 mm
Mounting dimension, height	60 mm
Reflection surface height	56 mm
Mounting dimension, thickness	8 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Coating	UV-protection
Type of fastening	Adhesive Through-hole mounting

Environmental data
Ambient temperature, operation

Certifications	
Degree of protection	IP 40

Classification	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467