







Front



Back















#### ■ Features

- Charger for lead-acid batteries (flooded, Gel and AGM) and li-ion batteries (lithium iron and lithium manganese)
- Built-in 3 stage programmable charging curve
- · Universal AC input / Full range
- · Built-in active PFC function
- · Fanless design, cooling by free air convection
- Built-in temperature compensation function
- Protection: Short circuit / Over voltage / Over temperature / Battery under voltage / Battery over voltage / Battery reverse polarity protection
- 3 years warranty

## Applications

- · Radio system backup solution
- · Electric scooter charger
- Surveillance system


#### **■** GTIN CODE

MW Search: https://www.meanwell.com/serviceGTIN.aspx

## Description

ENC-180 is a single output 180W AC/DC desktop type charger with 3 stage charging curve. In addition to the embedded pre-defined charging curves, the default curve is programmable and thus able to accommodate different types of batteries, such as lead-acid batteries (gel, flooded and AGM) and li-ion batteries (lithium iron and lithium manganese). With the rugged mechanical design along with the high efficiency circuitry, ENC-180 operates for the ambient temperature range -30~+70°C under free air convection.

## **■** Model Encoding






#### SPECIFICATION

MODEL		ENC-180-12	ENC-180-24	ENC-180-48	
	BOOST CHARGE VOLTAGE(Vboost)(default)	14.4V	28.8V	57.6V	
	FLOAT CHARGE VOLTAGE(Vfloat)(default)	13.8V	27.6V	55.2V	
	CHARGE VOLTAGE RANGE Note.3	9 ~ 15V	18 ~ 30V	36 ~ 60V	
	OUTPUT CURRENT(CC) (default)	12A	6A	3A	
DUTPUT	RATED POWER	172.8W	172.8W	172.8W	
	RECOMMENDED BATTERY CAPACITY (AMP HOURS) Note.4	45 ~ 125AH	25 ~ 65AH	15 ~ 35AH	
	LEAKAGE CURRENT FROM BATTERY (Typ.)	<1mA			
	VOLTAGE RANGE Note.5	90 ~ 264VAC 127 ~ 370VDC			
	FREQUENCY RANGE	47 ~ 63Hz			
	POWER FACTOR (Typ.)	PF>0.98/115VAC, PF>0.95/230VAC at full load			
NPUT	EFFICIENCY (Typ.)	91%	92%	93%	
	AC CURRENT (Typ.)	1.9A/115VAC 0.95A/230VAC			
	INRUSH CURRENT (Typ.)	COLD START 70A at 230VAC			
	LEAKAGE CURRENT	<3.5mA/240VAC			
	SHORT CIRCUIT Note.6	Protection type: Shut down O/P voltage,	re-nower on to recover		
		15.5 ~ 18.2V	31 ~ 36.5V	62.1 ~ 72.9V	
ROTECTION	OVER VOLTAGE Note.7	Protection type: Shut down and latch off		12.0	
	REVERSE POLARITY	By internal fuse	orp reliage, to power on to receive		
	OVER TEMPERATURE	Shut down O/P voltage, recovers automatically after temperature goes down			
UNCTION	TEMPERATURE COMPENSATION	7 1 0			
FUNCTION	WORKING TEMP.	-30 ~ +70°C (Refer to "Derating Curve")			
		,			
NVIDONMENT	WORKING HUMIDITY	20 ~ 95% RH non-condensing			
NVIRONMENT		-40 ~ +85°C, 10 ~ 95% RH non-condensing			
	TEMP. COEFFICIENT	±0.05%/°C (0~50°C)			
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes			
	SAFETY STANDARDS	IEC62368-1, UL62368-1, EAC TP TC 004, BSMI CNS14336-1 approved; Meet BS EN/EN62368-1			
	WITHSTAND VOLTAGE	I/P-O/P:3KVAC I/P-FG:2KVAC O/P-I			
	ISOLATION RESISTANCE	I/P-O/P, I/P-FG, O/P-FG:100M Ohms / 500VDC / 25°C / 70% RH			
		Parameter	Standard	Test Level / Note	
		Conducted	BS EN/EN55032 (CISPR32) / FCC PART15 (CISPR22)		
	EMC EMISSION	Radiated	BS EN/EN55032 (CISPR32) / FCC PART15 (CISPR22)	Class B	
		Harmonic Current	BS EN/EN61000-3-2		
SAFETY &		Voltage Flicker	BS EN/EN61000-3-3		
EMC		BS EN/EN55035, BSMI CNS13438			
Note 8)		Parameter	Standard	Test Level / Note	
		ESD	BS EN/EN61000-4-2	Level 3, 8KV air ; Level 2, 4KV contact	
		Radiated	BS EN/EN61000-4-3	Level 2, 3V/m	
	EMC IMMUNITY	EFT / Burst	BS EN/EN61000-4-4	Level 2, 1KV	
		Surge	BS EN/EN61000-4-5	Level 2, 1KV/Line-Line,Level 3, 2KV/Line-Ea	
		Conducted	BS EN/EN61000-4-6	Level 2, 3Vrms	
		Magnetic Field	BS EN/EN61000-4-8	Level 1, 1A/m	
		Voltage Dips and Interruptions	BS EN/EN61000-4-11	>95% dip 0.5 periods, 30% dip 25 period >95% interruptions 250 periods	
	MTBF	1445.6K hrs min. Telcordia SR-332 (Bellcore) ; 155.9K hrs min. MIL-HDBK-217F (25°C)			
OTHERS	DIMENSION	192*178*45.5mm (L*W*H)			
	PACKING	1.15Kg; 10pcs/12.5Kg /1.34CUFT			
NOTE	Modification for charger spe     All parameters NOT special     This is the range when prog     This is MEAN WELL's sugg	ecification may be required for different battery specification. Please contact battery vendor and MEAN WELL for details.  ally mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.  begramming Vboost or Vfloat by using SBP-001, the smart battery charging programmer.  gested range. Please consult your battery manufacturer for their suggestions about maximum charging current limitation.  under low input voltages. Please check the derating curve for more details.			

- 6. This protection mechanism is specified for the case the short circuit occurs after the charger is turned on.
- 7. Each model incorporates a MCU-controlled dynamic over voltage protection, which is about 115% of Vboost over Constant Current stage and Constant Voltage stage whereas 115% of Vfloat over Float stage.
- 8. The battery charger is considered as an independent unit, but the final equipment still need to re-confirm that the whole system complies with the EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com)
- 9. The ambient temperature derating of 3.5°C/1000m with fanless models and of 5°C/1000m with fan models for operating altitude higher than 2000m(6500ft).
- \*\* Product Liability Disclaimer: For detailed information, please refer to https://www.meanwell.com/serviceDisclaimer.aspx




### ■ Block Diagram



## ■ Derating Curve

## ■ Static Characteristics






#### ■ Function Manual

#### 1. Charging Curve

- \* This series provides a 3 stage charging. The default curve is programmable, whereas other pre-defined curves can be activated by the means of the DIP switch; please refer to the table below and the Mechanical Specification.
- \*\* To accommodate the parameters of the charging curve, SBP-001, the smart battery charging programmer designed by MEAN WELL, and a personal computer are needed. Please contact MEAN WELL for details.
- O Default 3 stage charging curve



© Suitable for lead-acid batteries (flooded, Gel and AGM) and Li-ion batteries (lithium iron and lithium manganese).


#### © Embedded 3 stage charging curve

MODEL	Description	CC(default)	Vboost	Vfloat
12V	Default, programmable		14.4	13.8
	Pre-defined, gel batter	12A	14	13.6
	Pre-defined, flooded battery	IZA	14.2	13.4
	Pre-defined, AGM battery		14.5	13.5
	Default, programmable		28.8	27.6
24V	Pre-defined, gel battery	6A	28	27.2
240	Pre-defined, flooded battery		28.4	26.8
	Pre-defined, AGM battery		29	27
	Default, programmable		57.6	55.2
48V	Pre-defined, gel battery	3A	56	54.4
40V	Pre-defined, flooded battery		56.8	53.6
	Pre-defined, AGM battery	ined, AGM battery		54

#### 2. Front Panel LED Indicators & Corresponding Signal at Function Pins

LED	Description
Green	Float (stage 3)
Orange	Charging (stage 1 or stage 2)







Case No. 252 Unit:mm

45.5

() LED

SWITCH - O 4.3





## Terminal Pin No. Assignment (TB1):

Pin No.	Assignment
1,2	+V
3.4	-V

Note: Please use wires with a cross section of  $0.5 - 4.0 \text{ mm}^2$  ( $12 \sim 20 \text{AWG}$ ) for connection. Recommended wires strip length is 9 mm and screw torque is 4.0 lb-inch ( $0.4 \sim 0.5 \text{Nm}$ ).

#### DIP SW:

1	2	Description	
OFF	OFF	Default, programmable	
ON	OFF	Pre-defined, Gel battery	
OFF	ON	Pre-defined, flooded battery	
ON	ON	Pre-defined, AGM battery	

# Connector Pin No. Assignment (CN31): HRS DF11-6DP-2DS or equivalent

Pin No.	Assignment	Mating Housing	Terminal
1	Prog-+3.3V	g a g a g a a a a a a a a a a a a a a a	
2	Prog- GND		
3	Prog-RX	HRS DF11-6DS	HRS DF11-**SC
4	Prog-TX	or equivalent	or equivalent
5	RTH+		
6	RTH-		



## ■ Accessory List

	Quantity	
1	NTC sensor wire	1
2	NTC mating wire	1

