

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier** 600283 Part A
- **Trade name:** 2-component methyl acrylate adhesive
- **Article number:** 4317784464963/1, 4317784464970/1
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
- **Sector of Use**
SU21 Consumer uses: Private households / general public / consumers
SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Application of the substance / the mixture** Activator
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
E/D/E - Einkaufsbuero Deutscher Eisenhaendler GmbH
EDE Platz 1
D-42389 Wuppertal
Germany

Tel. +49 202 6096-0
e-mail: sdb@ede.de
- **Further information obtainable from:** Product safety department
- **1.4 Emergency telephone number:** Giftinformationszentrum Mainz – Tel.: +49 (6131) 19240

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
Flam. Liq. 2 H225 Highly flammable liquid and vapour.
Skin Corr. 1A H314 Causes severe skin burns and eye damage.
Skin Sens. 1 H317 May cause an allergic skin reaction.
STOT SE 3 H335 May cause respiratory irritation.
Aquatic Chronic 3 H412 Harmful to aquatic life with long lasting effects.

2.2 Label elements

- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.

Hazard pictograms

GHS02 GHS05 GHS07

- **Signal word** Danger

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 1)

· Hazard-determining components of labelling:

 methacrylic acid
 α,α -dimethylbenzyl hydroperoxide

· Hazard statements

 H225 Highly flammable liquid and vapour.
 H314 Causes severe skin burns and eye damage.
 H317 May cause an allergic skin reaction.
 H335 May cause respiratory irritation.
 H412 Harmful to aquatic life with long lasting effects.

· Precautionary statements

 P101 If medical advice is needed, have product container or label at hand.
 P102 Keep out of reach of children.
 P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
 P271 Use only outdoors or in a well-ventilated area.
 P280 Wear protective gloves/protective clothing/eye protection/face protection.
 P301+P330+P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
 P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water.
 P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P310 Immediately call a POISON CENTER/doctor.
 P403+P233 Store in a well-ventilated place. Keep container tightly closed.
 P405 Store locked up.
 P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

· 2.3 Other hazards
· Results of PBT and vPvB assessment

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Chemical characterisation: Mixtures
· Description: Mixture of substances listed below with nonhazardous additions.

· Dangerous components:

CAS: 79-41-4 EINECS: 201-204-4 Index number: 607-088-00-5	methacrylic acid ⚠ Acute Tox. 3, H311 ⚠ Skin Corr. 1A, H314; Eye Dam. 1, H318 ⚠ Acute Tox. 4, H302; Acute Tox. 4, H332; STOT SE 3, H335	1-<10%
CAS: 82339-26-2	Urethanmethacrylat-Oligomer ⚠ Skin Irrit. 2, H315; Eye Irrit. 2, H319	1-<10%

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31











Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 2)

CAS: 128-37-0 EINECS: 204-881-4	Butylated hydroxytoluene  Aquatic Acute 1, H400; Aquatic Chronic 1, H410  Acute Tox. 4, H302	1-<1.5%
CAS: 80-15-9 EINECS: 201-254-7 Index number: 617-002-00-8 Reg.nr.: 01-2119475796-19-xxxx	α,α -dimethylbenzyl hydroperoxide  Org. Perox. E, H242  Acute Tox. 3, H331  STOT RE 2, H373  Skin Corr. 1B, H314  Aquatic Chronic 2, H411  Acute Tox. 4, H302; Acute Tox. 4, H312	1-<2.5%
CAS: 98-59-9 EINECS: 202-684-8	tosyl chloride  Eye Dam. 1, H318  Skin Irrit. 2, H315	1-<3%

- **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

• 4.1 Description of first aid measures

- **General information:** Immediately remove any clothing soiled by the product.

• **After inhalation:**

Supply fresh air.
Seek medical treatment in case of complaints.

• **After skin contact:**

Immediately wash with water and soap and rinse thoroughly.
If skin irritation continues, consult a doctor.

• **After eye contact:**

Rinse opened eye for several minutes under running water. Then consult a doctor.
Seek medical treatment.

- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.

• 4.2 Most important symptoms and effects, both acute and delayed

No further relevant information available.

• 4.3 Indication of any immediate medical attention and special treatment needed

No further relevant information available.

SECTION 5: Firefighting measures

• 5.1 Extinguishing media

• **Suitable extinguishing agents:**

CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

- **For safety reasons unsuitable extinguishing agents:** Water with full jet

(Contd. on page 4)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 3)

- **5.2 Special hazards arising from the substance or mixture** No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** Wear self-contained respiratory protective device.
- **Additional information**
Dispose of fire debris and contaminated fire fighting water in accordance with official regulations.
Cool endangered receptacles with water spray.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
Ensure adequate ventilation
Keep away from ignition sources.
- **6.2 Environmental precautions:**
Prevent seepage into sewage system, workpits and cellars.
Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Ensure adequate ventilation.
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Do not flush with water or aqueous cleansing agents
Use neutralising agent.
Dispose contaminated material as waste according to item 13.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

* SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about fire - and explosion protection:**



Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Provide solvent resistant, sealed floor.
Store only in the original receptacle.

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 4)

Provide floor trough without outlet.

- **Information about storage in one common storage facility:** Store away from oxidising agents.
- **Further information about storage conditions:** Store in cool, dry conditions in well sealed receptacles.
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **8.1 Control parameters**
- **Additional information about design of technical facilities:** No further data; see item 7.
- **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
Keep away from foodstuffs, beverages and feed.
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
Avoid contact with the eyes and skin.
- **Respiratory protection:**
Use suitable respiratory protective device in case of insufficient ventilation - filter A2
- **Protection of hands:**



Protective gloves

Only use chemical-protective gloves with CE-labelling of category III.

- **Material of gloves**
Butyl rubber, BR
Nitrile rubber, NBR
Recommended thickness of the material: ≥ 0.4 mm
- **Penetration time of glove material**
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Recommendation: safety glasses with side protection shield
- **Body protection:** Protective work clothing

EU
(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 5)

SECTION 9: Physical and chemical properties**· 9.1 Information on basic physical and chemical properties****· General Information****· Appearance:****Form:** Highly viscous**Colour:** Whitish**· Odour:** Characteristic**· Odour threshold:** Not determined.**· pH-value:** Not determined.**· Change in condition****Melting point/freezing point:** Undetermined.**Initial boiling point and boiling range:** Undetermined.**· Flash point:** 15 °C**· Flammability (solid, gas):** Not applicable.**· Decomposition temperature:** Not determined.**· Auto-ignition temperature:** Product is not selfigniting.**· Explosive properties:** Product is not explosive. However, formation of explosive air/vapour mixtures are possible.**· Explosion limits:****Lower:** Not determined.**Upper:** Not determined.**· Oxidising properties** Not determined.**· Vapour pressure:** Not determined.**· Density at 20 °C:** 0.97 g/cm³**· Relative density** Not determined.**· Vapour density** Not determined.**· Evaporation rate** Not determined.**· Solubility in / Miscibility with water:**

Not miscible or difficult to mix.

· Partition coefficient: n-octanol/water: Not determined.**· Viscosity:****Dynamic at 20 °C:** 140000 mPas**Kinematic:** Not determined.

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 6)

- **Solvent separation test:**
VOC (EC) % 2.93 %
- **9.2 Other information** No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** Reacts with oxidising agents.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

LD/LC50 values relevant for classification:**CAS: 79-41-4 methacrylic acid**

Oral	LD50	1,332 mg/kg (mouse)
Dermal	LD50	500 mg/kg (rabbit)

CAS: 128-37-0 Butylated hydroxytoluene

Oral	LD50	890 mg/kg (rat)
------	------	-----------------

CAS: 80-15-9 α,α -dimethylbenzyl hydroperoxide

Oral	LD50	382 mg/kg (rat)
Dermal	LD50	500 mg/kg (rat)
Inhalative	LC50/4h	220 ppm (rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation**
Causes severe skin burns and eye damage.
- **Serious eye damage/irritation**
Causes severe skin burns and eye damage.
- **Respiratory or skin sensitisation**
May cause an allergic skin reaction.

(Contd. on page 8)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 7)

- **Additional toxicological information:**
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**
May cause respiratory irritation.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information· **12.1 Toxicity**· **Aquatic toxicity:****CAS: 80-15-9 α,α -dimethylbenzyl hydroperoxide**

LC50 (96h) 3.9 mg/L (Oncorhynchus mykiss)

EC50/24h 7 mg/l (daphnia)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Harmful to fish
- **Additional ecological information:**
- **General notes:**
Must not reach sewage water or drainage ditch undiluted or unneutralised.
Harmful to aquatic organisms
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water
Do not allow product to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

— EU —

(Contd. on page 9)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 8)

SECTION 13: Disposal considerations

13.1 Waste treatment methods:

Containers can be recycled if completely empty; if not, dispose product/containers as dangerous waste. Observe local regulations.

European waste catalogue

08 04 09*	waste adhesives and sealants containing organic solvents or other hazardous substances
15 01 10*	packaging containing residues of or contaminated by hazardous substances

SECTION 14: Transport information

14.1 UN-Number**ADR, IMDG, IATA**

UN2924

14.2 UN proper shipping name**ADR**UN2924 FLAMMABLE LIQUID, CORROSIVE, N.O.S.
(METHYL METHACRYLATE MONOMER, STABILIZED,
METHACRYLIC ACID, STABILIZED)**IMDG**FLAMMABLE LIQUID, CORROSIVE, N.O.S. (METHYL
METHACRYLATE MONOMER, STABILIZED,
METHACRYLIC ACID, STABILIZED)**IATA**

FLAMMABLE LIQUID, CORROSIVE, N.O.S.

14.3 Transport hazard class(es)**ADR****Class**

3 (FC) Flammable liquids.

Label

3+8

IMDG**Class**

3 Flammable liquids.

Label

3/8

IATA**Class**

3 Flammable liquids.

Label

3 (8)

(Contd. on page 10)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 9)

- **14.4 Packing group**
 - **ADR, IMDG, IATA** II

 - **14.5 Environmental hazards:**
 - **Marine pollutant:** No

 - **14.6 Special precautions for user** Warning: Flammable liquids.
 - **Hazard identification number (Kemler code):** 338
 - **EMS Number:** F-E, S-C
 - **Segregation groups** Acids
 - **Stowage Category** B
 - **Stowage Code** SW2 Clear of living quarters.

 - **14.7 Transport in bulk according to Annex II of Marpol and the IBC Code** Not applicable.

 - **Transport/Additional information:**
-
- **ADR**
 - **Limited quantities (LQ)** 1L
 - **Excepted quantities (EQ)** Code: E2
Maximum net quantity per inner packaging: 30 ml
Maximum net quantity per outer packaging: 500 ml

 - **Transport category** 2
 - **Tunnel restriction code** D/E
-
- **IMDG**
 - **Limited quantities (LQ)** 1L
 - **Excepted quantities (EQ)** Code: E2
Maximum net quantity per inner packaging: 30 ml
Maximum net quantity per outer packaging: 500 ml

 - **UN "Model Regulation":** UN 2924 FLAMMABLE LIQUID, CORROSIVE, N.O.S. (METHYL METHACRYLATE MONOMER, STABILIZED, METHACRYLIC ACID, STABILIZED), 3 (8), II

SECTION 15: Regulatory information

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** Methanol
- **Seveso category** P5c FLAMMABLE LIQUIDS

- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 5,000 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 50,000 t

- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3

· **DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II**

None of the ingredients is listed.

(Contd. on page 11)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 15.12.2020

Version number 303

Revision: 15.12.2020

Trade name: 2-component methyl acrylate adhesive

(Contd. of page 10)

· National regulations:**· Information about limitation of use:**

Employment restrictions concerning pregnant and lactating women must be observed.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· Relevant phrases

H242 Heating may cause a fire.

H302 Harmful if swallowed.

H311 Toxic in contact with skin.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H315 Causes skin irritation.

H318 Causes serious eye damage.

H319 Causes serious eye irritation.

H331 Toxic if inhaled.

H332 Harmful if inhaled.

H335 May cause respiratory irritation.

H373 May cause damage to organs through prolonged or repeated exposure.

H400 Very toxic to aquatic life.

H410 Very toxic to aquatic life with long lasting effects.

H411 Toxic to aquatic life with long lasting effects.

· Contact: sdb@ede.de**· Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Flam. Liq. 2: Flammable liquids – Category 2

Org. Perox. E: Organic peroxides – Type E/F

Acute Tox. 4: Acute toxicity – Category 4

Acute Tox. 3: Acute toxicity – Category 3

Skin Corr. 1A: Skin corrosion/irritation – Category 1A

Skin Corr. 1B: Skin corrosion/irritation – Category 1B

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Dam. 1: Serious eye damage/eye irritation – Category 1

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

Skin Sens. 1: Skin sensitisation – Category 1

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

STOT RE 2: Specific target organ toxicity (repeated exposure) – Category 2

Aquatic Acute 1: Hazardous to the aquatic environment - acute aquatic hazard – Category 1

Aquatic Chronic 1: Hazardous to the aquatic environment - long-term aquatic hazard – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

· * Data compared to the previous version altered.