



SIMATIC S7-1500, ANALOG OUTPUT MODULE AQ 2 X U/I ST; 16 BITS OF RESOLUTION, ACCURACY 0.3 %; 2 CHANNELS IN GROUPS OF 2; DIAGNOSIS, SUBSTITUTE VALUE INCL. FRONT CONNECTOR PUSH-IN, FEEDING ELEMENT, SHIELDING ELEMENT, SHIELDING CLAMP

Product type designation

General information

HW functional status	E01
Firmware version	V1.0.0

Product function	
• I&M data	Yes; I&M0 to I&M3

Engineering with	
• STEP 7 TIA Portal can be configured/integrated as of version	V13 / V13.0.2
• STEP 7 can be configured/integrated as of version	V5.5 SP3 / -
• PROFIBUS as of GSD version/GSD revision	V1.0 / V5.1
• PROFINET as of GSD version/GSD revision	V2.3 / -

Operating mode	
• MSO	Yes

CiR - Configuration in RUN

Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes

Supply voltage

Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes

Input current

Current consumption, max.	110 mA; with 24 V DC supply
Power	
Power available from the backplane bus	0.65 W
Power losses	
Power loss, typ.	2.7 W
Analog outputs	
Number of analog outputs	2
Voltage output, short-circuit protection	Yes
Voltage output, short-circuit current, max.	24 mA
Current output, no-load voltage, max.	22 V
Cycle time (all channels), min.	3.2 ms; independent of number of activated channels
Output ranges, voltage	
• 0 to 10 V	Yes
• 1 V to 5 V	Yes
• -10 V to +10 V	Yes
Output ranges, current	
• 0 to 20 mA	Yes
• -20 mA to +20 mA	Yes
• 4 mA to 20 mA	Yes
Connection of actuators	
• for voltage output two-wire connection	Yes
• for voltage output four-wire connection	Yes
• for current output two-wire connection	Yes
Load impedance (in rated range of output)	
• with voltage outputs, min.	1 k Ω ; 0.5 k Ω m at 1 to 5 V
• with voltage outputs, capacitive load, max.	1 μ F
• with current outputs, max.	750 Ω
• with current outputs, inductive load, max.	10 mH
Cable length	
• shielded, max.	800 m; for current, 200 m for voltage
Analog value generation for the outputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Conversion time (per channel)	0.5 ms
Settling time	
• for resistive load	1.5 ms
• for capacitive load	2.5 ms
• for inductive load	2.5 ms
Errors/accuracies	

Output ripple (based on output area, bandwidth 0 to 50 kHz), (+/-)	0.02 %
Linearity error (relative to output range), (+/-)	0.15 %
Temperature error (relative to output range), (+/-)	0.002 %/K
Crosstalk between the outputs, max.	-100 dB
Repeat accuracy in steady state at 25 °C (relative to output area), (+/-)	0.05 %
Operational limit in overall temperature range	
• Voltage, relative to output area, (+/-)	0.3 %
• Current, relative to output area, (+/-)	0.3 %
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to output area, (+/-)	0.2 %
• Current, relative to output area, (+/-)	0.2 %
Isochronous mode	
Isochronous operation (application synchronized up to terminal)	No
Interrupts/diagnostics/status information	
Substitute values connectable	Yes
Alarms	
• Diagnostic alarm	Yes
Diagnostic messages	
• Diagnostics	Yes
• Monitoring the supply voltage	Yes
• Wire break	Yes; Only for output type "current"
• Short circuit	Yes; Only for output type "voltage"
• Overflow/underflow	Yes
Diagnostics indication LED	
• RUN LED	Yes; Green LED
• ERROR LED	Yes; Red LED
• Monitoring of the supply voltage (PWR-LED)	Yes; Green LED
• Channel status display	Yes; Green LED
• for channel diagnostics	Yes; Red LED
• for module diagnostics	Yes; Red LED
Electrical isolation channels	
• between the channels	No
• between the channels and the backplane bus	Yes
• between the channels and the load voltage L+	Yes
Permissible potential difference	
between MANA and M internally (UISO)	75 V DC/60 V AC (base isolation)
between S- and MANA (UCM)	+/- 8 V
Isolation	

Isolation checked with	707 V DC (type test)
Decentralized operation	
Prioritized startup	No
Dimensions	
Width	25 mm
Height	147 mm
Depth	129 mm
Weights	
Weight, approx.	200 g
other	
Note:	Supplied incl. 40-pole push-in front connectors
last modified:	12.03.2015