

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 30

Revision: 16.09.2019

**SECTION 1: Identification of the substance/mixture and of the company/undertaking**

- **1.1 Product identifier**
- **Trade name:** MOTIP® CYCLING CHAIN SPRAY SPORT 200 ML
- **Article number:** 000292
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**  
No further relevant information available.
- **Sector of Use**  
SU21 Consumer uses: Private households / general public / consumers  
SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category** PC24 Lubricants, greases, release products
- **Process category**  
PROC7 Industrial spraying  
PROC11 Non industrial spraying
- **Application of the substance / the mixture** Lubricant
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
MOTIP DUPLI B.V.  
Wolframweg 2  
NL- 8471 XC Wolvega  
The Netherlands  
Tel: +31 (0)561 694400  
Fax: +31 (0)561 694411  
e-mail: msds@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:**  
+31 (0)561-694400 (09:00h - 17:00h)

UK: NPIS National Poisons Information Centre Tel: +44 0344 892 0111

**SECTION 2: Hazards identification**

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.



GHS09 environment

Aquatic Chronic 2 H411 Toxic to aquatic life with long lasting effects.



GHS07

Skin Irrit. 2 H315 Causes skin irritation.  
STOT SE 3 H336 May cause drowsiness or dizziness.

(Contd. on page 2)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 30

Revision: 16.09.2019

Trade name: **MOTIP® CYCLING CHAIN SPRAY SPORT 200 ML**

(Contd. of page 1)

· **2.2 Label elements**· **Labelling according to Regulation (EC) No 1272/2008**

The product is classified and labelled according to the CLP regulation.

· **Hazard pictograms**

GHS02    GHS07    GHS09

· **Signal word** *Danger*· **Hazard-determining components of labelling:***pentane**Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, <5% n-hexane*· **Hazard statements***H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.**H315 Causes skin irritation.**H336 May cause drowsiness or dizziness.**H411 Toxic to aquatic life with long lasting effects.*· **Precautionary statements***P101 If medical advice is needed, have product container or label at hand.**P102 Keep out of reach of children.**P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.**P211 Do not spray on an open flame or other ignition source.**P251 Do not pierce or burn, even after use.**P260 Do not breathe spray.**P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.**P501 Dispose of contents / container in accordance with regional regulations.*· **2.3 Other hazards**· **Results of PBT and vPvB assessment**· **PBT:** Not applicable.· **vPvB:** Not applicable.\* **SECTION 3: Composition/information on ingredients**· **3.2 Chemical characterisation: Mixtures**· **Description:** Mixture of substances listed below with nonhazardous additions.· **Dangerous components:**

CAS: 109-66-0 EINECS: 203-692-4 Index number: 601-006-00-1 Reg.nr.: 01-2119459286-30	pentane Flam. Liq. 2, H225 Asp. Tox. 1, H304 Aquatic Chronic 2, H411 STOT SE 3, H336	25-<50%
CAS: 74-98-6 EINECS: 200-827-9 Index number: 601-003-00-5 Reg.nr.: 01-2119486944-21	propane Flam. Gas 1, H220 Press. Gas (Comp.), H280	12.5-<20%

(Contd. on page 3)

-GB-







**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 30

Revision: 16.09.2019

**Trade name: MOTIP® CYCLING CHAIN SPRAY SPORT 200 ML**

		(Contd. of page 2)
EC number: 921-024-6 Reg.nr.: 01-2119475514-35	Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, <5% n-hexane  Flam. Liq. 2, H225  Asp. Tox. 1, H304  Aquatic Chronic 2, H411  Skin Irrit. 2, H315; STOT SE 3, H336	12.5-<20%
CAS: 106-97-8 EINECS: 203-448-7 Index number: 601-004-00-0 Reg.nr.: 01-2119474691-32	butane  Flam. Gas 1, H220 Press. Gas (Comp.), H280	12.5-<20%
CAS: 75-28-5 EINECS: 200-857-2 Index number: 601-004-00-0 Reg.nr.: 01-2119485395-27	isobutane  Flam. Gas 1, H220 Press. Gas (Comp.), H280	12.5-<20%

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

#### SECTION 4: First aid measures

- **4.1 Description of first aid measures**
- **After inhalation:** In case of unconsciousness place patient stably in side position for transportation.
- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.
- **After eye contact:** Rinse opened eye for several minutes under running water.
- **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.
- **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

#### SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture**  
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters -**
- **Protective equipment:** Mouth respiratory protective device.

#### SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Mount respiratory protective device.  
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:**  
Inform respective authorities in case of seepage into water course or sewage system.
- **6.3 Methods and material for containment and cleaning up:**  
Dispose contaminated material as waste according to item 13.  
Ensure adequate ventilation.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

#### SECTION 7: Handling and storage

- **7.1 Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.

(Contd. on page 4)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 30

Revision: 16.09.2019

Trade name: **MOTIP® CYCLING CHAIN SPRAY SPORT 200 ML**

(Contd. of page 3)

- **Information about fire - and explosion protection:**  
Do not spray onto a naked flame or any incandescent material.  
Keep ignition sources away - Do not smoke.  
Keep respiratory protective device available.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**  
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 2 B
- **7.3 Specific end use(s)** No further relevant information available.

## SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.

### 8.1 Control parameters

- **Ingredients with limit values that require monitoring at the workplace:**

#### 109-66-0 pentane

WEL	Long-term value: 1800 mg/m <sup>3</sup> , 600 ppm
-----	---

#### 106-97-8 butane

WEL	Short-term value: 1810 mg/m <sup>3</sup> , 750 ppm Long-term value: 1450 mg/m <sup>3</sup> , 600 ppm Carc (if more than 0.1% of buta-1.3-diene)
-----	---

- **Additional information:** The lists valid during the making were used as basis.

### 8.2 Exposure controls

#### Personal protective equipment:

#### General protective and hygienic measures:

- Keep away from foodstuffs, beverages and feed.
- Immediately remove all soiled and contaminated clothing
- Wash hands before breaks and at the end of work.
- Do not inhale gases / fumes / aerosols.
- Avoid contact with the skin.
- Avoid contact with the eyes and skin.

#### Respiratory protection:

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

#### Protection of hands:

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation. Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

#### Material of gloves

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

#### Penetration time of glove material

Butyl rubber gloves with a thickness of 0.4 mm are resistant to:  
Acetone: 480 min

(Contd. on page 5)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 30

Revision: 16.09.2019

**Trade name: MOTIP® CYCLING CHAIN SPRAY SPORT 200 ML**

(Contd. of page 4)

Butyl acetate: 60 min

Ethyl acetate: 170 min

Xylene: 42 min

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:** Not required.

**SECTION 9: Physical and chemical properties**

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

· **Form:** Aerosol  
· **Colour:** Light brown

· **Odour:** Solvent-like

· **Odour threshold:** Not determined.

· **pH-value:** Not determined.

· **Change in condition**

· **Melting point/freezing point:** Undetermined.

· **Initial boiling point and boiling range:** Not applicable, as aerosol.

· **Flash point:** Not applicable, as aerosol.

· **Flammability (solid, gas):** Not applicable.

· **Ignition temperature:** 285 °C (545 °F)

· **Decomposition temperature:** Not determined.

· **Explosive properties:** Not determined.

· **Explosion limits:**

· **Lower:** 0.6 Vol %  
· **Upper:** 10.9 Vol %

· **Vapour pressure at 20 °C (68 °F):** 3500 hPa (2625.2 mm Hg)

· **Density at 20 °C (68 °F):** 0.6 g/cm<sup>3</sup> (5 lbs/gal)

· **Relative density:** Not determined.

· **Vapour density:** Not determined.

· **Evaporation rate:** Not applicable.

· **Solubility in / Miscibility with water:**

Not miscible or difficult to mix.

· **Partition coefficient: n-octanol/water:** Not determined.

· **Viscosity:**

· **Dynamic:** Not determined.  
· **Kinematic:** Not determined.

· **Solvent content:**

· **Organic solvents:** 85.0 %

· **VOC (EC):** ---  
523.6 g/l

· **VOC-EU%** 85.00 %

· **Solids content:** 0.0 %

· **9.2 Other information:** No further relevant information available.

-GB

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 30

Revision: 16.09.2019

Trade name: **MOTIP® CYCLING CHAIN SPRAY SPORT 200 ML**

(Contd. of page 5)

**SECTION 10: Stability and reactivity**

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

**SECTION 11: Toxicological information**

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

- **LD/LC50 values relevant for classification:**

**Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, <5% n-hexane**

Oral	LD50	>5840 mg/kg (rat)
Dermal	LD50	>2920 mg/kg (rab)
Inhalative	LC50 / 4h	>25.2 mg/l (rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation**  
Causes skin irritation.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**  
May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

**SECTION 12: Ecological information**

- **12.1 Toxicity**

- **Aquatic toxicity:**

**Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, <5% n-hexane**

EC50 / 48 h	3 mg/l (daphnia magna)
EC50 / 72 h	30-100 mg/l (algae)
LC50 / 96 h	11.4 mg/l (fish)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Toxic for fish
- **Additional ecological information:**
- **General notes:**  
Not hazardous for water.  
Also poisonous for fish and plankton in water bodies.  
Toxic for aquatic organisms
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

(Contd. on page 7)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 30

Revision: 16.09.2019

Trade name: **MOTIP® CYCLING CHAIN SPRAY SPORT 200 ML**

(Contd. of page 6)

· **12.6 Other adverse effects** No further relevant information available.

### SECTION 13: Disposal considerations

· **13.1 Waste treatment methods**· **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· **European waste catalogue**

20 01 13*	solvents
15 01 04	metallic packaging

· **Uncleaned packaging:**· **Recommendation:**

Disposal must be made according to official regulations.

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

Do not spray on a naked flame or any incandescent material.

### SECTION 14: Transport information

· **14.1 UN-Number**· **ADR, IMDG, IATA**

UN1950

· **14.2 UN proper shipping name**· **ADR**· **IMDG**

1950 AEROSOLS, ENVIRONMENTALLY HAZARDOUS AEROSOLS (PENTANES, Hydrocarbons, C6-C7, n-alkanes, isoalkanes, cyclics, &lt;5% n-hexane), MARINE POLLUTANT

· **IATA**

AEROSOLS, flammable

· **14.3 Transport hazard class(es)**· **ADR**· **Class**

2 5F Gases.

· **Label**

2.1

· **IMDG**· **Class**

2.1

· **Label**

2.1

· **IATA**· **Class**

2.1

· **Label**

2.1

(Contd. on page 8)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 30

Revision: 16.09.2019

Trade name: **MOTIP® CYCLING CHAIN SPRAY SPORT 200 ML**

(Contd. of page 7)

· <b>14.4 Packing group</b> · <b>ADR, IMDG, IATA</b>	<i>not regulated</i>
· <b>14.5 Environmental hazards:</b> · <b>Marine pollutant:</b> · <b>Special marking (ADR):</b>	<i>Symbol (fish and tree)</i> <i>Symbol (fish and tree)</i>
· <b>14.6 Special precautions for user</b> · <b>Danger code (Kemler):</b> · <b>EMS Number:</b> · <b>Stowage Code</b>  · <b>Segregation Code</b>	<i>Warning: Gases.</i> <i>-</i> <i>F-D,S-U</i> <i>SW1 Protected from sources of heat.</i> <i>SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters.</i> <i>SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4.</i> <i>For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2.</i> <i>For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.</i>
· <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b>	<i>Not applicable.</i>
· <b>Transport/Additional information:</b>	
· <b>ADR</b> · <b>Limited quantities (LQ)</b> · <b>Excepted quantities (EQ)</b>	<i>1L</i> <i>Code: E0</i> <i>Not permitted as Excepted Quantity</i> <i>Code: E0</i> <i>Not permitted as Excepted Quantity</i>
· <b>Transport category</b> · <b>Tunnel restriction code</b>	<i>2</i> <i>D</i>
· <b>IMDG</b> · <b>Limited quantities (LQ)</b> · <b>Excepted quantities (EQ)</b>	<i>1L</i> <i>Code: E0</i> <i>Not permitted as Excepted Quantity</i> <i>Code: E0</i> <i>Not permitted as Excepted Quantity</i>
· <b>UN "Model Regulation":</b>	<i>UN 1950 AEROSOLS, 2.1, ENVIRONMENTALLY HAZARDOUS</i>

### SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **Seveso category**  
*P3a FLAMMABLE AEROSOLS*  
*E2 Hazardous to the Aquatic Environment*
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3

(Contd. on page 9)

GB



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 30

Revision: 16.09.2019

**Trade name: MOTIP® CYCLING CHAIN SPRAY SPORT 200 ML**

(Contd. of page 8)

- **National regulations:**

- **Other regulations, limitations and prohibitive regulations**

- **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients is listed.

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

## SECTION 16: Other information

*This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.*

- **Relevant phrases**

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H280 Contains gas under pressure; may explode if heated.

H304 May be fatal if swallowed and enters airways.

H315 Causes skin irritation.

H336 May cause drowsiness or dizziness.

H411 Toxic to aquatic life with long lasting effects.

- **Department issuing SDS:** R&D legislation and regulatory advisor

- **Contact:** msds@nl.motipdupli.com

- **Abbreviations and acronyms:**

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Flam. Gas 1: Flammable gases – Category 1

Aerosol 1: Aerosols – Category 1

Press. Gas (Comp.): Gases under pressure – Compressed gas

Flam. Liq. 2: Flammable liquids – Category 2

Skin Irrit. 2: Skin corrosion/irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

Asp. Tox. 1: Aspiration hazard – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

- **\* Data compared to the previous version altered.**

GB