

## Flat spiral lathe chuck DURO-M DIN 6350, shape A

Hand chuck, for rear screw fittings



### Application:

The Duro-M is a manually operated rotary lathe chuck with spiral ring and through hole. It is mainly used on conventional lathes for machining turned parts.

### Execution:

- Chuck body (and all other components) made of steel
- Centric clamping
- High clamping force
- High concentricity
- Optimised for weight and mass inertia
- Minimum interference contour
- Three-jaw lathe chuck
- The Duro-M is also available with double jaw guide as an option.

### Advantage:

- Workpieces with different clamping diameters can be clamped very quickly and without repositioning the jaws.
- Control edge
- Use on conventionally clamping, horizontal and vertical lathes as well as milling machines, rotary tables and dividers.

### Delivery:

Ref. no. 22386011-22386072 Scroll lathe chuck 3-jaws with drilling and turning jaws

Ref. no. 22411021-22411081 Scroll lathe chuck 3-jaws with plain jaws and reverse top jaws.

The matching chuck key is included in the scope of delivery.



<b>Art. no.</b>	<b>22411 021</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	185310
<b>Outer diameter</b>	100
<b>Number of jaws</b>	3 PCS
<b>DIN</b>	6350-1
<b>Clearance hole</b>	20 mm
<b>Pitch circle diameter</b>	83
<b>Centring diameter</b>	70
<b>Square width</b>	8
<b>Depth</b>	3
<b>Length 2</b>	47 mm
<b>Height</b>	53.6 mm
<b>Length</b>	18 mm
<b>Max. rotation speed</b>	6300
<b>Tension force</b>	27
<b>Max. torque</b>	60 Nm
<b>Weight</b>	3.038 kg
<b>Gross Weight</b>	3.038 kg
<b>Product Group</b>	203

### EAN

4019208526928