

## Short taper flange

Made of cast iron



### Application:

For retroactive fastening of lathe chucks.

### Execution:

- Ready-machined on machine side and chuck side, spindle heads with bayonet fastening in accordance with DIN ISO 702-3 (formerly DIN 55027).

<b>Art. no.</b>	<b>22505 120</b>
<b>Brand</b>	BISON
<b>Manufacturer Part Number</b>	358230171700
<b>Flange diameter</b>	250 mm
<b>Taper shank size</b>	8
<b>Pitch circle diameter</b>	224 mm
<b>Taper diameter</b>	139.735 mm
<b>Drill hole</b>	136.1 mm
<b>Ratio</b>	200 mm
<b>Number of bolts</b>	6/4 pieces
<b>Flange thickness</b>	28 mm
<b>Thread dimension</b>	M12 x 6
<b>Gross Weight</b>	7.045 kg
<b>Product Group</b>	221

