

Data Sheet

135pcs 3:1 Heat shrinking adhesive lined tube with heat shrink solder splice connector - assortment

This range of heat shrink tube and heat solder connectors are particularly suitable for hobbyists, craftsmen, field service, service workshops, laboratory, and the cable repairing needs. 115 pieces of shrinking ratio 3:1 standard shrinking tube for a range of application diameter from 1.6 to 12.7 mm. Hot-melt adhesive lined tubing in the Black color.

20 pieces of shrinking ratio 2:1 heat solder connectors can be used for insulation, protective covering, as well as repair of cables and lines, and much more be used.



3:1 Adhesive Lined Heat Shrink Tube

Inner diameter \varnothing	After shrinking \varnothing	Tube length	Color	Quantity
1.6 mm	0.5 mm	32 mm	Black	35 pcs
2.4 mm	0.8 mm	32 mm	Black	25 pcs
3.2 mm	1.0 mm	32 mm	Black	20 pcs
4.8 mm	1.6 mm	32 mm	Black	12 pcs
6.4 mm	2.2 mm	32 mm	Black	8 pcs
7.9 mm	2.7 mm	32 mm	Black	6 pcs
9.5 mm	3.2 mm	32 mm	Black	5 pcs
12.7 mm	4.2 mm	32 mm	Black	4 pcs

Operating Temperature: -45 ~110°C

Minimum shrink temperature: 90°C

Full recovery temperature: 125°C

Heat Shrinking Solder Seal Splice Connector

Inner diameter \varnothing	Wire range	Tube length	Color	Quantity
1.7 mm	0.25 - 0.34 mm ²	25 mm	White	5 pcs
2.7 mm	0.5 - 1.0 mm ²	40 mm	Red	5 pcs
4.5 mm	1.5 - 2.5 mm ²	40 mm	Blue	5 pcs
6.0 mm	4.0 - 6.0 mm ²	40 mm	Yellow	5 pcs

Shrinking ratio: 2:1

Operating Temperature: -55 ~105°C

Minimum shrink temperature: 60°C

Full recovery temperature: 110°C

Full melting temperature of solder: 115°C