

# **TINA-SC-RS**

~14° spot beam

### **SPECIFICATION:**

Dimensions	Ø 16.2 mm
Height	9.9 mm
Fastening	clips
ROHS compliant	yes 🛈



PRODUCT DATASHEET

CP17594\_TINA-SC-RS

# LEDiL

MATERIALS:

Component TINA2-RS TINA-SC-HLD


### **Type** Single lens Holder

Material	Colour	Finish
PMMA	clear	
PC	black	

### **ORDERING INFORMATION:**

Component		Qty in box	MOQ	MPQ	Box weight (kg)
CP17594_TINA-SC-RS	Single lens	2400	240	240	5.0
» Box size: 300 x 250 x 250 mm					





R

See also our general installation guide: www.ledil.com/installation\_guide



# **OPTICAL RESULTS (SIMULATED):**

LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	CLR6A-TKW 21.0° / 40.0° 91 % 4.9 cd/lm 1 RGBW	99° 99° 99° 99° 99° 99° 99° 99° 99° 99°
LED FWHM / FWTM	XP-E2 10.0° / 20.0°	27 26 26 20
Efficiency Peak intensity LEDs/each optic Light colour	91 % 21 cd/lm 1 White	64 64 64 67
Required components:		200 00 120 XX
LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	XP-L HI 14.0° / 28.0° 91 % 11.3 cd/lm 1 White	20 20 20 20 20 20 20 20 20 20
CREE LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour Required components:	XP-L2 22.0° / 42.0° 86 % 4.2 cd/lm 1 White	



# **OPTICAL RESULTS (SIMULATED):**

		50° 50°
LED	XQ-E HI	73
FWHM / FWTM	10.0° / 18.0°	
Efficiency	89 %	60° 60°
Peak intensity	25.1 cd/lm	
LEDs/each optic	1	12800
Light colour	White	65 Gzt
Required components:		
		36° 22000 30°
OSRAM Opto Semiconductors		90° <b>A</b> 50°
LED	OSLON Square CSSRM2/CSSRM3	
FWHM / FWTM	16.0° / 31.0°	3. 2.
Efficiency	89 %	50° 500'
Peak intensity	9.3 cd/lm	$\tilde{\mathbf{x}} \neq \mathbf{z}$
LEDs/each optic	1	$  \times / /   \wedge \times  $
Light colour	White	gr
Required components:		6130
		$\times$ / $\vee$ $\times$
		30° <u>9000</u> 30° 30°
OSRAM Opto Semiconductors		50° A 50°
LED	SFH 4715AS	23-
FWHM / FWTM	21.0° / 32.0°	60°
Efficiency	88 %	
LEDs/each optic	1	
Light colour	IR	ger er
Required components:		4833
		6130
		30 <sup>4</sup> 30 <sup>6</sup> 30 <sup>6</sup>
OSRAM Opto Semiconductors		90* 90*
LED	SFH 4715S	
FWHM / FWTM	17.0° / 28.0°	75
Efficiency	89 %	
Peak intensity	9.5 cd/lm	
LEDs/each optic	1	$  \times / /   \wedge \times  $
Light colour	IR	9°
Required components:		6120
		36* 36*



# **OPTICAL RESULTS (SIMULATED):**

SAMSU	VG	90* <b>0</b> *
LED	LH351B	
FWHM / FWTM	16.0° / 31.0°	75*
Efficiency	90 %	
Peak intensity	8.4 cd/lm	3000
LEDs/each optic	1	
Light colour	White	
Required components:		6130
		36* 35* 0° 15* 35*
		15 0 15
		50° A 50°
	Z8Y22	
SEOUL SEMICONDUCTOR	Z8Y22 16.0° / 36.0°	77
seoul semiconductor LED		
seoul semiconductor LED FWHM / FWTM	16.0° / 36.0°	77
seoul semiconductor LED FWHM / FWTM Efficiency	16.0° / 36.0° 76 %	77
seoul semiconductor LED FWHM / FWTM Efficiency Peak intensity	16.0° / 36.0° 76 % 6 cd/lm	7° 9° 9°
seoul semiconductor LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic	16.0° / 36.0° 76 % 6 cd/lm 1 White	7°
SEOUL SEMICONDUCTOR LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour	16.0° / 36.0° 76 % 6 cd/lm 1 White	7°
SEOUL SEMICONDUCTOR LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour	16.0° / 36.0° 76 % 6 cd/lm 1 White	75
seoul semiconductor LED FWHM / FWTM Efficiency Peak intensity LEDs/each optic Light colour	16.0° / 36.0° 76 % 6 cd/lm 1 White	75



#### **GENERAL INFORMATION:**

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

#### **MATERIALS:**

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

### PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

#### LEDiL Oy

Joensuunkatu 13 FI-24240 SALO Finland

#### LEDiL Inc. 228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd. # 405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

### Local sales and technical support www.ledil.com/ where\_to\_buy

**Shipping locations** Salo, Finland Hong Kong, China

#### **Distribution Partners** www.ledil.com/ where\_to\_buy