MOMENTARY ACTION, ATTRACTIVE & RUGGED FOR WET & DUSTY ENVIRONMENTS

The P9 Dome series pushbutton switches feature a contoured dome style pushbutton and share similar size and characteristics to the P7 series. Major differences are plastic housing construction and the availability of a shorting bar contact arrangement. There are two button versions: low button profile and high button profile. The P9 comes with a threaded case for hex nut mounting or with a snap-in case. The switch series features short behind panel depth. They also offer excellent mechanical and electrical performance while operating under severe conditions found in demanding applications.

The P9 Dome series is offered in dusttight and moistureproof sealed construction. One million mechanical operations and an electrical life of 25,000 operations at full rated load of 5 amps resistive or 3 amps inductive.

Watertight sealing is available simply by adding a "W" suffix to the part number to specify IP68S rating.

The P9 Dome series is available in standard and low-force double break snap-action and non-snap shorting bar models. All are momentary action. Special contact variations are available. High contact pressure and unique contact design provide low contact resistance for low level switching capability as well as full rated service. Solder, PC Pin, and 0.110" Quick Connect termination options are available.

Positive tactile feedback signaling the operator when the switch is operated is available in snap-action models but not shorting har models.

The P9 Dome series is a quality precision switch designed for use in panels, control grips, computers, instruments, heavy equipment and other demanding applications where attractive, rugged pushbutton switches are required.

Features:

- Attractive dome style button
- 2 button heights
- Double break or shorting bar, momentary action
- All plastic housing & button construction
- Threaded body or snap-in panel mounting
- Withstands extreme shock & vibration
- Positive tactile feedback contact transfer on snap-action models
- Solder, PC Pin & 0.110" Quick Connect terminal styles
- Moistureproof & dusttight to IP64 or watertight to IP68S
- UL recognized & CSA certified
- RoHS/WEEE/Reach compliant








Standard Characteri	stics/Ratings:				
ELECTRICAL RATINGS:					
Load	N.O./N.C.	2 Circuit			
Resistive	5A	4A			
Inductive	3A	2A			
DWV	1050Vrms				
Low Level	10mA @ 30mV				
Electrical Life:	25,000 cycles 5A @ 28VDC resistive snap-action				
Mechanical Life:	1,000,000 cycles				
Seal:	IP64 or IP68S				
Operating Temp Range:	-40°C to +85°C				
Operating Force:	Standard: 1.7 lbs. +/- 0.5 lb. Low Force: 12 oz +/- 4 oz Shorting Bar: 18 oz +/- 6 oz				
Total Travel:	0.080 inches max				
Overtravel:	0.010 inches min				
MATERIALS:					
Case:	Thermoplastic				
Button:	Thermoplastic				
Terminals:	Brass with gold ov	er silver			
Terminal Hardware:	None provided				
Mounting Hardware:	Hex nut, lockwash Panel gasket wher				

PUSHBUTTONS

CHOICE OF SNAP-ACTION & SHORTING BAR ACTION










Raised Dome Button Style

Flush Dome Button Style

Snap-In Case (PC Terminals Shown)









Component Side P.C. Mounting Pattern (As viewed from switch bottom)





Solder Terminals (Terminals not orientated to flat) **Threaded Case**



PC Pin (Orientated to case flats as shown) Snap-In Case

Recommended Panel Openings					
*Panel Thickness	Recommended 0	DIM. Across D-Flat			
0.024*	0.505	0.460			
0.031	0.505	0.460			
0.118*	0.505	0.460			
0.125	0.505	0.460			

^{*} Must use panel gasket 401669 supplied with the switch.

- Snap-in case allows front panel mounting into 0.024" or 0.118" thick panels using panel gasket 401669 or into 0.031" and 0.125" thick panels
- 0.110" Quick Connect terminals allow reliable, solderless wire connections
- Flush Neoprene Black Boot P/N 402339
- Raised Neoprene Black Boot P/N 402246
- Flush Silicone Translucent Boot P/N 402599-1
- Raised Silicone Translucent Boot P/N 402611-1

ORDERING INFORMATION:

Select the OTTO P9 series features that match your specific application. Standard and special features are shown at right. Specify your choice by building the OTTO Part Number code.

Example: P9-211121 specifies raised dome style button, threaded case, solder terminals, N.O. circuit form, standard snapaction, black case/bezel, red button.

P9 **Button & Case Style*****

1. Flush Dome & Threaded Case, Std. Finish 2. Raised Dome & Threaded Case, Std. Finish

3. Flush Dome & Snap-In Case, Std. Finish

4. Raised Dome & Snap-In Case, Std. Finish

5. Flush Dome & Threaded Case, Matte Finish 6. Raised Dome & Threaded Case, Matte Finish

7. Flush Dome & Snap-In Case, Matte Finish 8. Raised Dome & Snap-In Case, Matte Finish

* Add "W" suffix for watertight to IP68S (will include panel gasket)

** Contact factory for minimum requirement.

*** Contact factory for std./matte button/case combination options.

P9 PART NUMBER CODE

_					
	Terminal Style	Circuit Form	Switch Action	Case/ Bezel Color	Button Color
h	1. Solder 2. PC Pin 3. 0.110" Quick Connect	1. N.O. 2. N.C. ① 3. 2 Circuit ①	Standard Snap-Action Low Force Snap-Action Non-Snap Shorting Bar	1. Red 2. Black 3. Orange** 4. Yellow** 5. Green** 6. Blue** 7. Violet** 8. Gray**	1. Red 2. Black 3. Orange 4. Yellow 5. Green 6. Blue 7. Violet 8. Gray
				9. White	9. White

¹⁾ Not available in Shorting Bar version.