

SSRC clamping holder, positive, right

For longitudinal turning with CC indexable insert

ATORN[®]

Application

For longitudinal turning with CC indexable insert, 80°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 75°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces
- Very good surface quality for medium infeed and finishing



Art. no.	17830 821
ISO name	SCRC R/L 16 16 H12
Shaft height	16 mm
Shank width	16 mm
Length	100 mm
Length of head	24 mm
Programming size	17 mm
Suitable for indexable inserts	CC.. 1204..
Tool design	Left

EAN-Code

4050293562736