

ESD Basic swivel work chair with glide runners

Synthetic leather upholstery, ESD-capable in accordance with DIN EN 61340-5-1

bimos

Application:

The ESD-compliant work chair makes a key contribution to reliable ESD protection measures at electronic workstations. An optimum choice of materials and joining technologies mean that BIMOS ESD Basic chairs are protected against the occurrence of electrostatic charge. It also ensures that any charge carried by the user is reliably transferred to the conductive base.

Execution:

- Infinitely variable and user-friendly seat height adjustment via pneumatic spring with dust protection
- Ref. no. 143/146/149: Height-adjustable foot rest ring
- ESD-capable in accordance with DIN EN 61340-5-1

Advantage:

- Ergonomically shaped permanent contact backrest, height-adjustable

Art. no.	50128 148
Brand	BIMOS
Manufacturer Part Number	9151E-2571-521
Model	ESD-Basic
Material of seat/backrest	Faux leather
Min. seat height	460 mm
Max. seat height	620 mm
Min./max. seat height	460-620 mm
Base frame design	Five-star base with rollers
Adjustable in height	Yes
Height-adjustable backrest	Yes
Adjustable seat inclination	No
Replaceable cushion	No
With cushion	Yes
With armrests	Optional
With foot ring	No
With rising aid	No
Load-carrying capacity	120 kg
On castors	Yes
ESD-capable	Yes
Material of frame	Aluminium
Gloss level	Polished
Colour	Black
DIN	68877
Gross Weight	14.500 kg
Product Group	5AA



EAN

4016849374338