# SPECIFICATION FOR APPROVAL

承

認

書

Description : Piezo Audio Transducer

Kingstate Part No. : **KPEG163** 

Customer's Model No. :

Specification No. : PKD-2229

Number Of The Edition : 1.2

CUSTOMER'S APPROVED SIGNATURE			

## 志豐電子股份有限公司 KINGSTATE ELECTRONICS CORP.



Address: 10F, No. 69-11, Sec. 2, Chung Cheng E. Rd., Tamshui County, Taipei Hsien, Taiwan, R.O.C.

International sales dept.: TEL:886-2-2809-5651 FAX:886-2-2809-7151

Domestic sales dept.: TEL:886-2-2809-0668 FAX:886-2-28096748

http://www.kingstate.com.tw

Approved by	Checked by	Issued by
t in the	罗科的	Fei 1/27/05'


#### A.SCOPE 範疇

This specification applies piezo audio transducer, **KPEG163** 此規格書適用於壓電式蜂鳴器, **KPEG163** 

### B. SPECIFICATION 規格

No.	ltem	Unit	Specification	Condition
1	Operating Volt. 操作電壓	Vp-p	MAX 30	
2	Current consumption 消耗電流	mA	MAX 10	at 10Vp-p,square wave,4.8KHz.
3	Sound pressure level 輸出音壓	dB	MIN 80	at 10cm/10Vp-p,square wave,4.8KHz.
4	Electrostatic capacity		14,000 ± 30%	at 1KHz/1V
5	Operating temp. 操作溫度		-30 ~ +85	
6	Storage temp. 儲存溫度		-40 ~ +95	
7	Dimension 尺寸	mm	13.0 x H 2.5	See appearance drawing 請參照外觀尺寸圖
8	Weight (MAX) 重量	gram	0.35	
9	Material 材質		ABS UL-94 1/16" HB HIGH HEAT ( BLACK )	
10	Terminal 端 <del>了</del>		Wire type	See appearance drawing 請參照外觀尺寸圖
11	Environmental Protection Regulation 環保法規		ROHS	


### C. APPEARANCE DRAWING 外觀尺寸圖



Tol: ± 0.5 Unit: mm


志豐電子股份有限公司 KINGSTATE ELECTRONICS CORP 2/5 KPEG163

#### D. TYPICAL FREQUENCY RESPONSE CURVE 頻率響應曲線



#### E. MEASURING METHOD 測量方法

S.P.L. Measuring Circuit 音壓測試接線圖 Input Signal: 10Vp-p,4.8kHz, Square Wave 輸入信號: 10Vp-p,4.8kHz,方波



Mic: RION S.P.L meter UC30 or equivalent

Mic: RION 噪音計 UC30 或同等品

S.G: Hewlett Packard 33120A Function Generator or equivalent

S.G: Hewlett Packard 33120A 函數信號產生器或同等品

志豐電子股份有限公司 KINGSTATE ELECTRONICS CORP 3/5 KPEG163

### F. MECHANICAL CHARACTERISTICS 機械特性

No	ltem	Test Condition	Evaluation standard
1	Solderability 焊錫付著性	Stripped wires of lead wires are immersed in rosin for 5 seconds and then immersed in solder bath of +230±5 for 3±0.5 seconds. 裸線部份浸入松香溶液 5 秒後,再浸入+230±5 溶線射导射槽中 3±0.5 秒.	90% min. stripped wires shall be wet with solder.(Except the edge of terminal) 浸入裸線部份附著焊錫 90%以上.(末端斷面不算)
2	Soldering Heat Resistance 焊鍋耐索性	Stripped wires are immersed up to 1.5mm from insulation in solder bath of +300±5 for 3±0.5 seconds or +260±5 for 10±1 seconds, and then sounder shall be measured after being placed in natural condition for 4 hours. 距絕緣體 1.5mm 的位置,浸入+300±5 的焊緣槽 3±0.5 秒,或+260±5 的焊緣槽 10±1 秒.	
3	Lead Wire Pull Strength 線材拉力	The pull force shall be applied to double lead wire: Horizontal 3.0N for 30 seconds. Vertical 2.0N for 30 seconds. 雙線材水平方向施以 3.0N 的力量, 垂直方向施以 2.0N 的力量,各 30 秒	No damage and cutting off. 線材不鬆動,不脫落.
4	Vibration 振動症式驗	Buzzer shall be measured after being applied vibration of amplitude of 1.5mm with 10 to 55hz band of vibration frequency to each of 3 per-pendicular directions for 2 hours. 振動過波數10 55HZ、全振幅1.5mm於X.Y.Z3個方向,各2小時.	frequency/ current consumption should be in ±10% compared with initial ones .The SPL should
5	Drop test 落下測試	The part only shall be dropped from a height of 75cm onto a 40mm thick wooden board 3 times in 3 axes (X.Y.Z). (a total of 9 times). 單體從75 公分高處, X.Y.Z.3 個方向,各3回,落於40mm厚木板上.	be in ±10dB compared with initial one. 諧振頻率與消耗電流變化量須在 ±10%內. 輸出音壓變化量須在 ±10dB 內.

### G. ENVIRONMENT TEST 環境測試

No	ltem	Test Condition	Evaluation standard
1	High temp. test 高溫測試	After being placed in a chamber at +95 for 240 hours 置於+95 環境中 240 小時	
2	Low temp. test 低溫測試	After being placed in a chamber at -40 for 240 hours 置於-40 環境中 240 小時	
3	Humidity test 相對濕度測試	After being placed in a chamber at +40 and 90±5% relative humidity for 240 hours 置於+40 ,相對濕度 90±5% 環境中 240 小時	Being placed for 4 hours at +25, buzzer shall be
4	Temp. cycle test 溫度循環試驗	The part shall be subjected to 5 cycles. One cycle shall be consist of: 單體承受溫度循環測試 5 次,其循環內容如圖示:  +95  -40  0.5hr  0.5hr  0.5hr  0.5hr  0.5hr  0.5hr  0.25  3hours	measured. The value of oscillation frequency/ current consumption should be in ±10% compared with initial ones. The SPL should be in ±10dB compared with initial one. 經測試後,靜置於+25 (室溫)環境中4小時後,諧陽與率與消耗電流變化量須在±10%內. 輸出音壓變化量須在±10dB內.

#### H. RELIABILITY TEST 信賴性測試

No.	Item	Test condition	Evaluation standard
1	Operating life test 壽命測試	1.Continuous life test 高溫壽命測試(連續) 120 hours continuous operation at +70 with rated voltage applied. 在+70 環境下,以額定電壓連續操作 120 小時 2.Intermittent life test 室溫壽命測試(間歇) A duty cycle of 1 minute on, 1 minutes off, a minimum of 10000 times at room temp.(+25±2 ) and rated voltage applied 在室溫下(+25±2 ),以額定電壓操作,通電 1 分鐘/斷電 1 分鐘,測試 10000 次循環.	Being placed for 4 hours at +25 , buzzer shall be measured. The value of oscillation frequency/ current consumption should be in ±10% compared with initial ones .The SPL should be in ±10dB compared with initial one. 經測試後,靜置於+25 (室溫)環境中 4 小時後,諧振頻率與消耗電流變化量須在±10%內.輸出音壓變化量須在±10dB內.

c) Pressure: 860-1060mbar

#### **TEST CONDITION.**

Standard Test Condition

a) Temperature: +5 ~ +35 b) Humidity: 45-85% a) 温度: +5 ~ +35 b) 濕度: 45-85% b) 濕度: 45-85% a) Temperature: +25 ± 2 b) Humidity: 60-70% a) 温度: +25 ± 2 b) 濕度: 60-70% c) 氣壓: 860-1060mbar 一般測試條件 Judgement Test Condition : c) Pressure: 860-1060mbar 爭議時測試條件 : c) 氣壓: 860-1060mbar

#### I. PACKING STANDARD 包裝規格

