

4-830611-8 ✓ ACTIVE

LGH


TE Internal #: 4-830611-8

Circular Power Connectors, Lead Assembly, Operating Voltage  
10000 VDC, 16AWG Wire Size, Wire-to-Wire, Wire & Cable, Socket

[View on TE.com >](#)



Connectors > Power Connectors > Circular Power > Circular Power Connectors



Connector Product Type: **Lead Assembly**

Operating Voltage: **10000 VDC**

Wire Size: **16 AWG**

Connector System: **Wire-to-Wire**

Sealable: **No**

## Features

### Product Type Features

Connector Product Type	Lead Assembly
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

### Electrical Characteristics

Operating Voltage	10000 VDC
-------------------	-----------

### Body Features

Positive Stop Ferrule	Without
-----------------------	---------

### Contact Features

Contact Type	Socket
--------------	--------

### Termination Features

Termination Method to Wire & Cable	Pre-Terminated to Cable
------------------------------------	-------------------------

### Dimensions

Wire Size	16 AWG
Assembly Length	304.8 mm[12 in]

### Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

### Operation/Application



Shielded	No
----------	----

### Packaging Features

Packaging Method	Package
Packaging Quantity	20

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	<p>Current ECHA Candidate List: JAN 2021 (211)  Candidate List Declared Against: JUN 2020 (209)  SVHC &gt; Threshold:  Pb (4% in Contact/Component)</p> <p><b>Article Safe Usage Statements:</b>  Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</p>
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


### Customers Also Bought



TE Part #8-1879642-3  
H8 1K11 0.1% 5PPM



TE Part #YDTS26T11-35SA0000  
D38999: Straight Plug, 11-35 Insert



TE Part #3-87962-1  
64 MODII HORZ DR CE 100CL/115



TE Part #670713-000  
44A0141-16-MST4CS2275



TE Part #513559-000  
55FA0514-24-7L6



TE Part #6-146459-4  
14 MODII HDR SRST UNSHRD STKG



TE Part #1614379-5  
RN 0805 12K 0.1% 10PPM CUT  
LENGTH



TE Part #5-1676274-4  
RN 0805 27K 0.1% 10PPM 1K RL



TE Part #5054122017  
RNF-100-3/16-GY-STK



TE Part #1-1624317-0  
SP3 22R1 1% TAPED

## Documents

### Product Drawings

[LGH 1/2 SNGL MLD END](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_4-830611-8\\_AH.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-830611-8\\_AH.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-830611-8\\_AH.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages



[Products for Aerospace and Defense](#)

English

---

[Product Specifications](#)

[Product Specification](#)

English