

Miniature cutting insert type AX HC5640

For reverse internal boring

ATORN[®]

Application

For reverse internal boring in steel and (stainless steel) material groups at low to high cutting speeds and mid-range cutting conditions.

Version

- Solid carbide cutting insert with internal cooling

Advantage

- Robust cemented carbide grade for a broad application range
- Stable geometry optimised for reverse internal boring machining
- Ideal for use with low-performance machines and unstable cutting conditions



Art. No.	17123 150
ISO name	AX
Shaft diameter	4 mm
Length	51 mm
Clearance length	10 mm
Radius	0.1 mm
Programming size 2	0.5 mm
Programming size	1.3 mm
Min. bore diameter	3.1 mm
Machining direction	Left
Carbide type	HC5640
Material to be processed	Steel, Stainless steel, Non-ferrous metal, Cast metal

EAN-Code

4050293660760