

## SVVB clamp holder, positive neutral

For copy and longitudinal face turning using VB indexable inserts

**ATORN**<sup>®</sup>

### Application


For copy, longitudinal and face turning with VB indexable insert, 35°

### Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 72.5°, tip angle 35°, clearance angle 5°
- SVVBN 1212 F11

### Advantage

- Very streamlined geometry, optimised for contour lathe work
- Positive geometry for the body ensures low cutting forces
- Very good surface quality for medium infeed and finishing



<b>Art. No.</b>	<b>17836 205</b>
<b>ISO name</b>	SVVB N 2525 M16
<b>Shaft height</b>	25 mm
<b>Shank width</b>	25 mm
<b>Length</b>	150 mm
<b>Length of head</b>	37 mm
<b>Programming size</b>	13.1 mm
<b>Suitable for indexable inserts</b>	VB.. 1604..
<b>Tool design</b>	Neutral
<b>DIN</b>	4983

### EAN-Code

4050293127393