SAFETY DATA SHEET

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Trade name or designation of the mixture	HEAT SINK COMPOUND
Registration number	-
Synonyms	None.
Product code	BDS001215BU
Issue date	25-March-2022
Version number	1.0
Revision date	25-March-2022

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses	Lubricants
Uses advised against	None known.

1.3. Details of the supplier of the safety data sheet

Company name	CRC Industries Europe bv
Address	Touwslagerstraat 1 9240 Zele Belgium
Telephone	+32(0)52/45.60.11 hse@crcind.com www.crcind.com

Company name	CRC Industries UK Ltd.
Address	Wylds Road Castlefield Industrial Estate TA6 4DD Bridgwater Somerset United Kingdom
Telephone	+44 1278 727200
Fax	+44 1278 425644
E-mail	hse.uk@crcind.com
Website	www.crcind.com

1.4. Emergency telephone number Tel.:(+44)(0)1278 72 7200 (office hours: 9-17h CET)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

The mixture has been assessed and/or tested for its physical, health and environmental hazards and the following classification applies.

Classification according to Regulation (EC) No 1272/2008 as amended

Environmental hazards

Hazardous to the aquatic environment, acute aquatic hazard	Category 1	H400 - Very toxic to aquatic life.
Hazardous to the aquatic environment, long-term aquatic hazard	Category 1	H410 - Very toxic to aquatic life with long lasting effects.

2.2. Label elements

Label according to Regulation (EC) No. 1272/2008 as amended

Hazard pictograms

Signal word Warning

Hazard statements

H410 Very toxic to aquatic life with long lasting effects.

Precautionary statements

Prevention

P102 Keep out of reach of children.
P273 Avoid release to the environment.

Response

P391 Collect spillage.

Storage Not assigned.

Disposal

P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

Supplemental label information None.

2.3. Other hazards This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII. The product does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

Mixture

General information

Chemical name	%	CAS-No. / EC No.	REACH Registration No.	Index No.	Notes
Zinc oxide	25 - 50	1314-13-2 215-222-5	01-2119463881-32	030-013-00-7	#

Classification: Aquatic Acute 1;H400, Aquatic Chronic 1;H410

List of abbreviations and symbols that may be used above

#: This substance has been assigned Union workplace exposure limit(s).
M: M-factor
PBT: persistent, bioaccumulative and toxic substance.
vPvB: very persistent and very bioaccumulative substance.
All concentrations are in percent by weight unless ingredient is a gas. Gas concentrations are in percent by volume.

Composition comments The full text for all H-statements is displayed in section 16.

SECTION 4: First aid measures

General information Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

4.1. Description of first aid measures

Inhalation Move to fresh air. Call a physician if symptoms develop or persist.

Skin contact Wash off with soap and water. Get medical attention if irritation develops and persists.

Eye contact Rinse with water. Get medical attention if irritation develops and persists.

Ingestion Rinse mouth. Get medical attention if symptoms occur.

4.2. Most important symptoms and effects, both acute and delayed Headache. Nausea, vomiting. Coughing.

4.3. Indication of any immediate medical attention and special treatment needed Treat symptomatically.

SECTION 5: Firefighting measures

General fire hazards No unusual fire or explosion hazards noted.

5.1. Extinguishing media

Suitable extinguishing media Water fog. Foam. Dry chemical powder. Carbon dioxide (CO2).

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture During fire, gases hazardous to health may be formed.

5.3. Advice for firefighters

Special protective equipment for firefighters Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Special fire fighting procedures	Use water spray to cool unopened containers.
Specific methods	Use standard firefighting procedures and consider the hazards of other involved materials.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For non-emergency personnel	Wear appropriate protective equipment and clothing during clean-up.
For emergency responders	Keep unnecessary personnel away. Ensure adequate ventilation. Local authorities should be advised if significant spillages cannot be contained. For personal protection, see section 8 of the SDS.
6.2. Environmental precautions	Avoid release to the environment. Inform appropriate managerial or supervisory personnel of all environmental releases. Prevent further leakage or spillage if safe to do so. Avoid discharge into drains, water courses or onto the ground.
6.3. Methods and material for containment and cleaning up	The product is immiscible with water and will sediment in water systems. Prevent entry into waterways, sewer, basements or confined areas. Stop the flow of material, if this is without risk. Following product recovery, flush area with water.
6.4. Reference to other sections	For personal protection, see section 8 of the SDS. For waste disposal, see section 13 of the SDS.

SECTION 7: Handling and storage

7.1. Precautions for safe handling	Avoid prolonged exposure. Provide adequate ventilation. Wear appropriate personal protective equipment. Avoid release to the environment. Observe good industrial hygiene practices.
7.2. Conditions for safe storage, including any incompatibilities	Store in tightly closed container. Store away from incompatible materials (see Section 10 of the SDS). Storage class (TRGS 510): 13 (Non-combustible solids that cannot be assigned to any of the above storage classes)
7.3. Specific end use(s)	Not available.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

UK. EH40 Workplace Exposure Limits (WELs)

Components	Type	Value	Form
Zinc oxide (CAS 1314-13-2)	TWA	4 mg/m3	Respirable dust.
		10 mg/m3	Inhalable dust.

Biological limit values	No biological exposure limits noted for the ingredient(s).
Recommended monitoring procedures	Follow standard monitoring procedures.
Derived no effect levels (DNELs)	Not available.
Predicted no effect concentrations (PNECs)	Not available.

8.2. Exposure controls

Appropriate engineering controls	Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

General information	Personal protection equipment should be chosen according to the CEN standards and in discussion with the supplier of the personal protective equipment.
Eye/face protection	Wear safety glasses with side shields (or goggles). Use eye protection conforming to EN 166.
Skin protection	
- Hand protection	When handling the product wear chemical-resistant gloves (standard EN 374). The breakthrough time of the glove should be longer than the total duration of product use. If work lasts longer than the breakthrough time, gloves should be changed part-way through. Nitrile gloves are recommended. Suitable gloves can be recommended by the glove supplier.
- Other	Wear suitable protective clothing.
Respiratory protection	In case of insufficient ventilation, wear suitable respiratory equipment. Chemical respirator with organic vapour cartridge. (Filter type A)
Thermal hazards	Wear appropriate thermal protective clothing, when necessary.

Hygiene measures	Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.
Environmental exposure controls	Inform appropriate managerial or supervisory personnel of all environmental releases. Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. Fume scrubbers, filters or engineering modifications to the process equipment may be necessary to reduce emissions to acceptable levels.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	
Physical state	Solid.
Form	Paste.
Colour	White.
Odour	Characteristic odor.
Odour threshold	Not available.
pH	Not applicable.
Melting point/freezing point	Not available.
Initial boiling point and boiling range	Not available.
Flash point	> 340.0 °C (> 644.0 °F)
Evaporation rate	Not applicable.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	Not available.
Flammability limit - upper (%)	Not available.
Vapour pressure	< 0.01 kPa at 20°C
Vapour density	Not available.
Relative density	2.3 g/cm3 at 20°C
Solubility(ies)	
Solubility (water)	Insoluble in water
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Explosive properties	Not explosive.
Oxidising properties	Not oxidising.

9.2. Other information

VOC	0 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
10.2. Chemical stability	Material is stable under normal conditions.
10.3. Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
10.4. Conditions to avoid	Contact with incompatible materials.
10.5. Incompatible materials	Strong oxidising agents.
10.6. Hazardous decomposition products	Not available.

SECTION 11: Toxicological information

General information	Occupational exposure to the substance or mixture may cause adverse effects.

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.

Eye contact	Based on available data, the classification criteria are not met.
Skin contact	Based on available data, the classification criteria are not met.
Ingestion	May cause discomfort if swallowed. However, ingestion is not likely to be a primary route of occupational exposure.
Symptoms	Headache. Nausea, vomiting. Coughing.

11.1. Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met.

Components	Species	Test Results
Zinc oxide (CAS 1314-13-2)		
Acute		
Dermal		
LD50	Rabbit	> 2000 mg/l
Inhalation		
LC50	Mammal	2500 mg/m³
Oral		
LD50	Mouse	7950 mg/kg

Skin corrosion/irritation	Based on available data, the classification criteria are not met.
Serious eye damage/eye irritation	Based on available data, the classification criteria are not met.
Respiratory sensitisation	Based on available data, the classification criteria are not met.
Skin sensitisation	Based on available data, the classification criteria are not met.
Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Based on available data, the classification criteria are not met.
Reproductive toxicity	Based on available data, the classification criteria are not met.
Specific target organ toxicity - single exposure	Based on available data, the classification criteria are not met.
Specific target organ toxicity - repeated exposure	Based on available data, the classification criteria are not met.
Aspiration hazard	Based on available data, the classification criteria are not met.
Mixture versus substance information	Not available.

SECTION 12: Ecological information

12.1. Toxicity Very toxic to aquatic life with long lasting effects.

Components		Species	Test Results
Zinc oxide (CAS 1314-13-2)			
Acute			
	EC50	Selenastrum capricornutum (new name Pseudokirchnerella subca	0.137 mg/l, 72 hours
Aquatic			
Acute			
Crustacea	EC50	Daphnia magna	0.413 mg/l, 48 hours
Chronic			
Crustacea	NOEC	Daphnia magna	82 µg/l, 7 days

12.2. Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.
12.3. Bioaccumulative potential	
Partition coefficient n-octanol/water (log Kow)	Not available.
12.4. Mobility in soil	No data available.
12.5. Results of PBT and vPvB assessment	This mixture does not contain substances assessed to be vPvB / PBT according to Regulation (EC) No 1907/2006, Annex XIII.
12.6. Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Residual waste	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.
EU waste code	The Waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Disposal methods/information	Collect and reclaim or dispose in sealed containers at licensed waste disposal site. Do not allow this material to drain into sewers/water supplies. Do not contaminate ponds, waterways or ditches with chemical or used container. Dispose of contents/container in accordance with local/regional/national/international regulations.
Special precautions	Dispose in accordance with all applicable regulations.

SECTION 14: Transport information

ADR

14.1. UN number	UN3077
14.2. UN proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc oxide)
14.3. Transport hazard class(es)	
Class	9
Subsidiary risk	-
Hazard No. (ADR)	Not available.
Tunnel restriction code	E
14.4. Packing group	III
14.5. Environmental hazards	Yes
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

RID

14.1. UN number	UN3077
14.2. UN proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc oxide)
14.3. Transport hazard class(es)	
Class	9
Subsidiary risk	-
Label(s)	9
14.4. Packing group	III
14.5. Environmental hazards	Yes
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

ADN

14.1. UN number	UN3077
14.2. UN proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc oxide)
14.3. Transport hazard class(es)	
Class	9
Subsidiary risk	-
Label(s)	9
14.4. Packing group	III
14.5. Environmental hazards	Yes
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

IATA

14.1. UN number	UN3077
14.2. UN proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc oxide)
14.3. Transport hazard class(es)	
Class	9
Subsidiary risk	-
14.4. Packing group	III
14.5. Environmental hazards	Yes
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

IMDG

14.1. UN number	UN3077
14.2. UN proper shipping name	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S. (Zinc oxide), MARINE POLLUTANT
14.3. Transport hazard class(es)	
Class	9
Subsidiary risk	-
14.4. Packing group	III
14.5. Environmental hazards	
Marine pollutant	Yes
EmS	F-A, S-F
14.6. Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not applicable.

ADN; ADR; IATA; IMDG; RID



Marine pollutant

General information IMDG Regulated Marine Pollutant.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Retained direct EU regulations

Regulation (EC) No. 1005/2009 on substances that deplete the ozone layer, Annex I and II, as amended

Not listed.

Regulation (EU) 2019/1021 On persistent organic pollutants (recast), as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 1 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 2 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex I, Part 3 as amended

Not listed.

Regulation (EU) No. 649/2012 concerning the export and import of dangerous chemicals, Annex V as amended

Not listed.

Regulation (EC) No. 166/2006 Annex II Pollutant Release and Transfer Registry, as amended

Zinc oxide (CAS 1314-13-2)

Regulation (EC) No. 1907/2006, REACH Article 59(10) Candidate List as currently published by ECHA

Not listed.

Authorisations

Regulation (EC) No. 1907/2006, REACH Annex XIV Substances subject to authorization, as amended

Not listed.

Restrictions on use

Regulation (EC) No. 1907/2006, REACH Annex XVII Substances subject to restriction on marketing and use as amended

Not listed.

Other EU regulations

Directive 2012/18/EU on major accident hazards involving dangerous substances, as amended

Zinc oxide (CAS 1314-13-2)

Other regulations

The product is classified and labelled in accordance with Regulation (EC) 1272/2008 (CLP Regulation) as amended. This Safety Data Sheet complies with the requirements of Regulation (EC) No 1907/2006, as amended.

Follow national regulation for work with chemical agents in accordance with Directive 98/24/EC, as amended.

15.2. Chemical safety assessment No Chemical Safety Assessment has been carried out.

SECTION 16: Other information

List of abbreviations

ADN: European Agreement Concerning the International Carriage of Dangerous Goods by Inland Waterways.
ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.
ADR: European Agreement Concerning the International Carriage of Dangerous Goods by Road.
ATE: Acute Toxicity Estimate according to REGULATION (EC) No 1272/2008 (CLP).
CAS: Chemical Abstract Service.
Ceiling: Short Term Exposure Limit Ceiling value.
CEN: European Committee for Standardization.
CLP: Classification, Labeling and Packaging REGULATION (EC) No 1272/2008 on classification, labeling and packaging of substances and mixtures.
GWP: Global Warming Potential.
IATA: International Air Transport Association.
IBC Code: International Code for the Construction and Equipment of Ships Carrying Dangerous Chemicals in Bulk.
IMDG: International Maritime Dangerous Goods.
MAK: Threshold limit values Germany (Maximale Arbeitsplatzkonzentration - DFG).
MARPOL: International Convention for the Prevention of Pollution from Ships.
PBT: Persistent, bioaccumulative and toxic.
REACH: Registration, Evaluation and Authorization of Chemicals (REGULATION (EC) No 1907/2006 concerning Registration, Evaluation Authorization and Restriction of Chemicals).
RID: Regulations concerning the international carriage of dangerous goods by rail (Règlement International concernant le transport de marchandises dangereuses par chemin de fer).
RID: Regulations concerning the International Carriage of Dangerous Goods by Rail.
STEL: Short term exposure limit.
TLV: Threshold Limit Value.
TWA: Time Weighted Average.
VOC: Volatile organic compounds.
vPvB: Very persistent and very bioaccumulative.
STEL: Short-term Exposure Limit.

References Not available.

Information on evaluation method leading to the classification of mixture The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available.

Full text of any H-statements not written out in full under Sections 2 to 15 H410 Very toxic to aquatic life with long lasting effects.

Revision information None.

Training information Follow training instructions when handling this material.

Disclaimer CRC Industries Europe bvba cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.