



SIMATIC ET 200SP, BaseUnit BU20-P12+A0+4B, BU type B1, Packing unit: 1 unit, push-in terminals, without auxiliary terminals, bridged to the left, WxH: 20 mm x 117 mm

General information	
Product type designation	BU type B1
HW functional status	FS10 and higher
Supply voltage	
Rated value (DC)	See manual
<ul style="list-style-type: none"> For P1 and P2 bus For AUX bus for process terminals 	24 V 24 V; Equal potential group to P1/P2 bus or PE 24 V
Rated value (AC)	See manual
<ul style="list-style-type: none"> For P1 and P2 bus For AUX bus for process terminals 	230 V 230 V; Equal potential group to P1/P2 bus or PE 230 V
external protection for power supply lines	Yes
Mains filter	
<ul style="list-style-type: none"> integrated 	No
Current carrying capacity	
up to 60 °C, max.	10 A
For P1 and P2 bus, max.	10 A
For AUX bus, max.	10 A
For process terminals, max.	5 A
Hardware configuration	
Automatic encoding	Yes
Slots	
<ul style="list-style-type: none"> Number of slots 	1
Potential separation	
between backplane bus and supply voltage	Yes
between process terminals and supply voltage	Yes; Not applicable for process terminals 9 to 12
between power bus and supply voltage	Yes
Isolation	
Isolation tested with	3 100 V DC
Ambient conditions	
Ambient temperature during operation	
<ul style="list-style-type: none"> horizontal installation, min. horizontal installation, max. vertical installation, min. vertical installation, max. 	-30 °C 60 °C -30 °C 50 °C
Altitude during operation relating to sea level	
<ul style="list-style-type: none"> Installation altitude above sea level, max. 	2 000 m; On request: Installation altitudes greater than 2 000 m
connection method / header	
Terminals	

- Terminal type
- system-integrated shield connection
- Conductor cross-section, min.
- Conductor cross-section, max.
- Number of process terminals to I/O module
- Number of terminals to AUX bus
- Number of add-on terminals
- Number of terminals with connection to P1 and P2 bus

Push-in terminal
 No
 0.14 mm²; AWG 26
 2.5 mm²; AWG 14
 12; Pro slot
 0
 0
 0; Pro slot

Dimensions

Width	20 mm
Height	117 mm
Depth	35 mm

Weights

Weight, approx.	48 g
-----------------	------

last modified: 1/20/2023 