



## Section 1. Product and Company Identification.

**1.1 Model Number;** SCS700 v1  
**1.2 Description;** Cutting Compound Fine 500ml

**1.3 Manufacturer;**  
Sealey Group.  
Kempson Way,  
Bury St. Edmunds,  
Suffolk.  
IP32 7AR

**1.4 Emergency telephone number;** 44 (0) 1284 757 500 (Office Hours)

**Date of source compilation;** 08 February 2012

## Section 2. Hazards Identification.

**2.1 Classification of the substance or mixture.**  
Asp. Tox. 1, H304

**2.2 Label elements.**  
**Hazard pictogram(s)**



**Signal Word.** Danger

### **Hazard statements;**

H304 - May be fatal if swallowed and enters airways.  
EUH066 - Repeated exposure may cause skin dryness or cracking.

### **Precautionary statements;**

P301+P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.  
P331 - Do NOT induce vomiting.  
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes.  
Remove contact lenses, if present and easy to do. Continue rinsing.  
P314 - Get medical advice/attention if you feel unwell.

**2.3 Other hazards.**  
None identified



### Section 3. Substances.

3.1 Chemical Name (substance)	3.1 CAS No.	3.2 Concentration Weight	Classification	
			Hazard Class & Category Code	Hazard Statements
Distillates (petroleum), hydrotreated light; Kerosene	64742-47-8	5 - 10%	Asp. Tox. 1	H304

For full text of Phrases and Statements, see Section 16.

### Section 4. First Aid Measures.

#### 4.1 Description of first aid measures

##### Inhalation

Remove casualty from exposure ensuring one's own safety whilst doing so.

##### Skin Contact

Wash immediately with plenty of soap and water.

##### Eye Contact

Bathe the eye with running water for 15 minutes.

##### Ingestion

Do NOT induce vomiting.

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

#### 4.2. Most important symptoms and effects, both acute and delayed

Mildly irritating to respiratory system

In cases of severe exposure, dizziness, confusion, headache or stupor may develop

Mildly irritating to skin and eyes

Can cause damage to the eyes, skin and mucous membranes

#### 4.3. Indication of any immediate medical attention and special treatment needed

No information available.

### Section 5. Fire Fighting Measures.

#### 5.1. Extinguishing media

Foam, carbon dioxide or dry agent to extinguish.

#### 5.2. Special hazards arising from the substance or mixture

May give off noxious and toxic fumes in a fire

Smoke from fire is irritating. Take precautions to protect personnel from exposure

#### 5.3. Advice for fire-fighters

Keep container(s) exposed to fire cool by spraying with water

Vapours are heavier than air and may travel considerable distances to a source of ignition and flashback

Wear Breathing Apparatus





## Section 6. Accidental Release Measures.

### 6.1. Personal precautions, protective equipment and emergency procedures

Spillage causes slippery surfaces.

Shut off source of leak if safe to do so.

Ensure adequate ventilation.

### 6.2. Environmental precautions

Do not empty into drains

Do not allow to enter public sewers and watercourses - If contamination of drainage systems or water courses is unavoidable, immediately inform appropriate authorities

### 6.3. Methods and material for containment and cleaning up

Absorb spillage in inert material and shovel up

Place in appropriate container

Remove contaminated material to safe location for subsequent disposal

To clean the floor and all objects contaminated by this material use soap and water

### 6.4. Reference to other sections

See Section 7 for information on Safe Handling

See Section 8 for information of Personal Protective Equipment.

See Section 13 for information on disposal.

## Section 7. Handling and Storage.

### 7.1. Precautions for safe handling

Ensure adequate ventilation

Proper chemicals handling procedures should be adopted

### 7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated place

Store in a closed container.

Keep away from frost.

Store locked up.

### 7.3. Specific end use(s)

Intended for use as Cutting Compound Fine: Model Number identified in 1.1 with Description stated in 1.2.



## Section 8. Exposure Controls/Personal Protection.

### 8.1. Control parameters

P301+P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

P331 - Do NOT induce vomiting.

P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P314 - Get medical advice/attention if you feel unwell.

### 8.2. Exposure controls

#### Appropriate Engineering Controls

Ensure there is sufficient ventilation of the area.

#### Eye/Face Protection

Safety glasses with side shields or chemical safety goggles.

Ensure eye bath is to hand.

#### Skin Protection

EN 374 Chemical resistant protective gloves.

Wear suitable protective clothing.

#### Respiratory Protection

Self-contained breathing apparatus must be available in case of emergency.

## Section 9. Physical and Chemical Properties.

### 9.1. Information on basic physical and chemical properties

**The following information is not a technical specification or sales specification.**

(a) Appearance:	White viscous paste.
(b) Odour:	Characteristic.
(c) Odour threshold;	No information available.
(d) pH:	No information available.
(e) Melting point/freezing point;	No information available.
(f) Initial boiling point and boiling range;	No information available.
(g) Flash point;	No information available.
(h) Evaporation rate;	Not relevant.
(i) Flammability (solid, gas);	No information available.
(j) Upper/lower flammability or explosive limits;	No information available.
(k) Vapour pressure;	No information available.
(l) Vapour density;	Not relevant.
(m) Relative density;	Specific Gravity: 1.270
(n) Solubility(ies);	Soluble in water.
(o) Partition coefficient: n-octanol/water;	No information available.
(p) Auto-ignition temperature;	No information available.
(q) Decomposition temperature;	No information available.
(r) Viscosity;	16500 centipoise at 20°C
(s) Explosive properties;	No information available.
(t) Oxidising properties.	No information available.

### 9.2 Other information

No information available.



## Section 10. Stability and Reactivity.

**10.1.** Reactivity

This article is considered stable under normal conditions

**10.2.** Chemical stability

This article is considered stable under normal conditions

**10.3.** Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose.

**10.4.** Conditions to avoid

Keep away from frost

**10.5.** Incompatible materials

No hazardous reactions known if used for its intended purpose.

**10.6.** Hazardous decomposition products

No hazardous decomposition products known.

## Section 11. Toxicological Information.

**11.1.** Information on toxicological effects

No information available.

## Section 12. Ecological Information.

12.1. Toxicity

No information available.

12.2. Persistence and degradability

No information available.

12.3. Bioaccumulative potential

No information available.

12.4. Mobility in soil

No information available.

12.5. Results of PBT and vPvB assessment

No information available.

12.6. Other adverse effects

No information available.

## Section 13. Disposal Considerations.

13.1. Waste treatment methods

Dispose of in accordance with local authority regulations.

## Section 14. Transport Information.

ADR. International Carriage of Dangerous Goods by Road.

Not regulated.

IATA. International Air Transport Association.

Not regulated.

IMDG. International Maritime Dangerous Goods.

Not regulated.

## Section 15. Regulatory Information.

**15.1.** Safety, health and environmental regulations/legislation specific for the substance or mixture

No information available.

**15.2.** Chemical safety assessment

No information available.



**Section 16. Additional Information.**

Full text of Phrases and Statements used in Section 3;

H304 May be fatal if swallowed and enters airways.

The above information is believed to be accurate and represents the best information currently available.

No warranty is expressed or implied by the above information.

We assume no liability resulting from use of the above information.

The end user should conduct their own investigations to determine the suitability of the above information for their particular purpose.

Issue level	Date	Revisions
1	14/04/16	First issue.
2	27/03/17	Format only.

End of Safety Data Sheet.