## **MULTI-AXIS INDUCTIVE JOYSTICK**

**ORDER CODE** 



JC200-B with K1 handle

A compact, inductive joystick with a life in excess of 15 million operations and EMC immunity of 50V/m, the JC200 offers fingertip control in two axes.

Designed for use with an electronic controller, the inductive circuit inside the JC200 generates analogue signals proportional to the distance over which the handle is moved in either axis. This output is configured to provide signals for fault detection circuits within the controller, whilst a center tap provides an accurate voltage reference for the center position.

The inductive circuit can be mounted at 45° to the normal axis to provide reference signals for dual channel motor controllers.

The output voltage range can be further restricted in one or more directions, by the selection of the correct gate geometry. This can be used to limit, for example, the maximum speed of a vehicle when reversing around a corner.

Typical applications include the control of wheelchairs, fork lift trucks and agricultural machinery.

JC200 –	B - S - 1	- K1 - Y		
Mounting ————	_			
Gate ———				Coil Orientation
Voltage swing —				Handle
Mounting	В		P	
	Four hole square	flange	Two hole bezel flange	
Gates	S	R	N	
Shape	Square	Round	Notch	
Voltage Swing	1	2	3	
Input Voltage (Vs)	10Vdc	12Vdc	12Vdc	
Output Voltage Swing	±10%Vs	±8.3%Vs	±10%Vs	
Handles	КО	K1		
Shape	No handle	Standard knob		
Coil Orientation	Y	Z		
	Normal to Axis	45° to Axis		

Full deflection, 50mm above

flange with square gate

# 4 holes to suit 47.5 M3 screws HY AXIS 47.5 M3 screws M3 screws A41.0 M41.0 M4

## +Y AXIS +Y AXIS +Y AXIS +Y AXIS +Y AXIS +X AXIS -X AXIS -X

All dimensions in mm

## **Specifications**

MechanicalBreakout Force1NOperating Force2NMaximum Applied Force50N

Mechanical Angle of Movement  $\pm 18^{\circ}$  On axis with square gate fitted

Expected Life (Operations) >15 million

Mass 120g With K1 handle option

**Environmental** 

Operating Temperature Range  $-25^{\circ}\text{C}$  to  $+65^{\circ}\text{C}$ Storage Temperature Range  $-40^{\circ}\text{C}$  to  $+70^{\circ}\text{C}$ 

Environmental Sealing Above the Flange IP66 BSEN60529

EMC Immunity Level 50V/m 10MHz to 1GHz, 1KHz 80% sine wave modulation ESD Immunity Level ±25kV 10 discharges through air

Electrical

Supply Voltage Range (Vs) 0-8V, 0-10V or 0-12v Maximum 14Vdc

Output Impedance  $1k8\Omega$ 

Output Voltage Swing  $\pm 10\%$ Vs,  $\pm 8.3\%$ Vs with respect to the center tap

Error Signal >  $\pm 25\%$ Vs Center Tap Voltage 50%Vs  $\pm 1\%$  Center Tap Impedance 0.4k $\Omega$ 

Return to Center Voltage  $\pm 0.03$ Vs or 30mV, whichever is less

Resolution Infinit


Connection Flying Leads 200mm long (14 x 0.12 pvc)


**Termination Details** 

DescriptionWire colorPositive voltage supplyRedCenter tapGreenZero voltage supplyBlackX-axis output voltage signalBlueY-axis output voltage signalYellow

Note: Output signals should be referenced to the center tap voltage

### **Gate Options**





Alternative gate geometery can be developed to meet the needs of your potential application