

IWLAN RCOAX N-CONNECT MALE TERMINATION IMPEDANCE
50 OHM TI795-1N, 2.4 AND 5 GHZ TERMINATING RESISTOR 50
OHM FOR RCOAX CABLE



Electrical data

Number of electrical connections	1
Type of electrical connection	N-Connect male
Transmission frequency	0 ... 6 GHz
Impedance	50 Ω
Return loss / minimum	25 dB

Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> during operation 	-40 ... +70 °C
<ul style="list-style-type: none"> during storage 	-40 ... +70 °C
<ul style="list-style-type: none"> during transport 	-40 ... +70 °C
Protection class IP	IP 65

Design, dimensions and weight

Diameter	21 mm
Length	34.5 mm
Net weight	45 g

Standards, specifications, approvals

Certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net

- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

09.03.2015