Glass Fiber-Optic Cable Reflex Mode for P1XF

Part Number



Technical Data

| Optical Data | |
|-------------------------------|---------------------|
| Fiber Bundle Diameter | 3 mm |
| Working Distance | 100 mm |
| Light Spot Diameter | 10 mm |
| Fiber | Step Index |
| Fiber Distribution | statistical mixture |
| Mechanical Data | |
| Temperature Range | 060 °C |
| Bending Radius | 50 mm |
| Fiber-Optic Length | 1 m |
| Jacket Material | CuZn, nickel-plated |
| Fiber-Optic Cable Adapter No. | 01 |

- Compatible with the P1XF001 6-channel **Multispectral Sensor**
- Laid out for tight installation spaces
- Rugged design

In the scanning mode, the glass fiber-optic cables are compatible with the P1XF001 6-channel Multispectral Sensor. They're ideal for use in difficult to access locations and they detect colored objects.





