

### **Features**

- RoHS **Compliant**
- Universal 90V AC to 264V AC or 127V DC to 373V DC input voltage
- Accepts AC or DC input (dual-use of same terminal)
- Operating ambient temperature range: -40°C to +70°C
- Built-in active PFC function
- High I/O isolation test voltage up to 4000V AC
- Extremely low leakage current<0.1mA
- Stand-by power consumption<0.5W
- The base plate with conformal coating
- Output short circuit, over-current, over-voltage, over-temperature protection
- Installing in system of Safety Class I (with PE), Class II (no PE) is available
- Suitable for BF application
- Safety according to IEC/EN/UL62368, IEC/EN60335, IEC/EN61558, GB4943, IEC/EN/ES60601
- Withstand 300V AC surge input for 5s
- Operating altitude up to 5000m

These series is one of enclosed AC-DC switching power supply and suitable for all kinds of BF type (be accessible to patients) medical system equipment. It features universal AC input and at the same time accepts DC input voltage, cost-effective, low no load power consumption, high efficiency, high reliability and double or reinforced insulation. These converters offer excellent EMC performance and meet IEC/EN/UL62368, GB4943, IEC/EN60335, IEC/EN61558, IEC/EN/ ES60601 standards and they are widely used in areas of industrial, LED, street light control, electricity, security, telecommunications, smart home etc.

Selection Guide								
Part Number	Cool Mode	Output Power (W)	Nominal Output Voltage and Current (Vo/Io)	Output adj. Range (V)	Efficiency at 230VAC (%) Typ.	Max. Capacitive Load (μF)		
MPOF350-20B12-C	Air cooling	180	12V/15A	11.4-12.6		6000		
WF0F350-20B12-C	20.5CFM	300	12V/25A	11.4-12.0	92			
MPOF350-20B15-C	Air cooling	180	15V/12A	14.25-15.75	92	5000		
WPOF350-20B15-C	20.5CFM	325	15V/21.67A	14.25-15.75				
MPOF350-20B24-C	Air cooling	199.9	24V/8.33A	22.8-25.2		3200		
WF0F350-20B24-C	20.5CFM	350.4	24V/14.6A	22.0-25.2	93	3200		
MPOF350-20B27-C	Air cooling	199.8	27V/7.4A	25.65-28.35	93	2600		
MPOF350-20B27-C	20.5CFM	351	27V/13A	20.00-20.30		2600		
MPOF350-20B48-C	Air cooling	200.1	48V/4.17A	45 6 50 4	04	2000		
	20.5CFM	350.4	48V/7.3A	45.6-50.4	94	2000		

Note: 1.\*Under any conditions, the total power of the product should not exceed the rated power. When the output voltage is increased, the total output power cannot exceed the rated output power, when the output voltage is decreased, the output current cannot exceed the rated output current;

2.\*When measuring the full load efficiency, the fan should be connected to an external power supply. Fan loss is not included in the input power.



# 350W AC to DC Enclosed Switching Power Supply

## multicomp PRO

Input Specifications							
Item		Operating Conditions	Min.	Тур.	Max.	Unit	
Innut Valtage Denge	AC input	,	90		264	VAC	
Input Voltage Range	DC input	,	127 373	373	VDC		
Input Voltage Frequency		,	47		63	Hz	
Input Current	115VAC				4		
	230VAC	`			2	Α	
	115VAC	Caldatad		50		]	
Inrush Current	230VAC	Cold start		75	4 2		
Power Factor	115VAC	Full Load	0.98				
Power Factor	230VAC	Truii Load	0.95			]	
Leakage Current	240VAC		<0.1mA	<0.1mA; single failure<0.5mA			
Hot Plug				Unavailable			

## **Output Specifications**

Item	Operating (	Min.	Тур.	Max.	Unit		
Output Voltage Accuracy*	Full land varia	12V/15V		±3			
Output Voltage Accuracy	Full load range	24V/27V/48V		±2			
Line Regulation	Rated load			±0.5			
Load Regulation	0% - 100% load	0% - 100% load		±1			
		12V			120		
	20MHz bandwidth	15V			120	]	
Output Ripple & Noise*	(peak-to-peak value)	24V			150	mV	
	(peak-to-peak value)	27V			200		
		48V			250		
Temperature Coefficient		'		±0.03		%/°C	
Minimum Load		'	0			%	
Hold-up Time	220\/AC_full load	Air cooling	12	14		ms	
noid-up nine	230VAC, full load	20.5CFM	6	8			
Stand-by Power Consumption					0.5	W	
Short Circuit Protection	recover time <5s after the short circuit disappear		Hiccup, continuous, self-recover				
Over-current Protection				≥110%, self-recover			
	12V		≤15.0V (Output voltage turn off, re-power on for recover)				
	15V			tput voltage turn off, re-power on for recover)			
Over-voltage Protection	24V		≤30.0V (Output voltage turn off, re-pow- er on for recover)				
	27V		≤33.5V (Output voltage turn off, re-pow- er on for recover)				
	48V		≤59.5V (Output voltage turn off, re-power on for recover)				





Item	Operating Conditions	Min.	Тур.	Max.	Unit
Over-temperature Protection		Output voltage turn off, re-power o recover after the temperature dro			
Fan power	12V/15V/24V/48V	Offer output power of 12V/0.5A with output voltage accuracy ±15%			
	27V	Offer output power of 12V/0.5A with o put voltage accuracy -25% - +15%			

Note: 1.\* Output Voltage Accuracy: including setting error, line regulation, load regulation;

- 2.\* The "Tip and barrel method" is used for ripple and noise test, output parallel 10uF electrolytic capacitor and 0.1uF ceramic capacitor, please refer to AC-DC Converter Application Notes for specific information;
- 3.\* When the product works under light load (≤10%lo), in order to improve efficiency, the value of ripple & noise will be 1.5 times of the full load specification;
- 4.\* For all the above test items, please refer to our company standard "AC-DC Black Box Test Specification" for specific test specifications and methods;
- 5.\* For fan power connection method, please refer to pin 6/7 of the dimension drawing.

General Sp	ecifications	<b>3</b>					
Item		Operating Conditions		Min.	Тур.	Max.	Unit
Isolation Test	Input - ≟		2000				
	Input - output	Electric strength test for current <10mA	4000			VAC	
	Output - 🖶	Carrent Clonia	current < Torna				
1 1 0	Input - ≟	Ambient temperature: 2	100	] -			
Insulation Resistance	Input - output	Relative humidity: < 959	%RH, no condensation	100		-	МΩ
rtoolotarioo	Output - 🖶	Test voltage: 500V DC		100		-	
Operating Temp	perature			-40		+70	°C
Storage Tempe	rature			-40		+85	C
Storage Humidi	ity	Non condensing		10		95	%RH
Operating Hum	idity	Non-condensing		20		90	%КП 
Switching Frequency				-	] -	-	kHz
		Operating temperature	+50°C to +70°C	2.5		1	%/°C
Power Derating	1	derating	-40°C to +50°C	0			70/ C
Fower Deraung		Input voltage derating	90VAC - 100VAC	1		%/\/Δι	%/VAC
			100VAC - 264VAC	0			70/ VAC
Safety Standard				Meet IEC/ 1/IEC/EN6 EN60601- /CAN/CSA 3/ EN6060	61558-1 1/ES60 A-C22.2	/GB4943 601-1(3.1 No.6060	B-1/IEC/
Safety Certification				IEC/EN/UL62368/EN60601 (Pending		1 (Pending)	
Safety Class		CLASS I (with PE and r ed)/CLASS II (without F			st be connect-		
	Input - output			2 × MOPP			
Isolation level	Input - 🖶			1 × MOPP	)		
	Output - 🖶		1 × MOPP				
MTBF		MIL-HDBK-217F@25°C		≥300,000 h			





Mechanical Specifications					
Case Material	Metal (AL5052, SGCC)				
Dimensions	130mm × 86mm × 35mm				
Weight	430g (Typ.)				
Cooling Method*	Free air convection (180W/200W) / 20.5CFM (300W/350W)				
Note: *Please refer to the product characteristic curve for cooling method and power derating.					

## **Electromagnetic Compatibility (EMC)**

EMI*	CE	CISPR32/EN55032 CLASS B				
	RE	CISPR32/EN55032 CLASS B (Category I, CLASS B; Category II, CLASS A)				
	Harmonic current	IEC/EN61000-3-2 CLASS A				
EMS*	ESD	IEC/EN 61000-4-2 Contact ±8KV/Air ±15KV	Perf. Criteria A			
	RS	IEC/EN 61000-4-3 10V/m	Perf. Criteria A			
	EFT	IEC/EN 61000-4-4 ±4KV	Perf. Criteria A			
	Surge	IEC/EN 61000-4-5 ±2KV/±4KV	Perf. Criteria A			
	CS	IEC/EN61000-4-6 10 Vr.m.s	Perf. Criteria A			
	DIP	IEC/EN61000-4-11 0%, 70%	perf. Criteria B			


Note: 1.\*The power supply is considerated a component as part of system, all EMC items are tested on a metal plate (L x W x H, 360mm x 360mm x 1mm). Power supply should be combined with final equipment for EMC confirmation; 2.\*Category I products with PE, which must be connected, category II products without PE.

### **Product Characteristic Curve**

### MPOF350-20B12-C (full load 300W with Forced Air)


### Output Power Percentage(%) Temperature Derating Curve 100 20.5CFM Input Voltage Air cooling 90-264VAC 127-373VDC 30 50 Ambient temperature (°C)


### MPOF350-20B15-C (full load 325W with Forced Air)




MPOF350-20B24/27/48-C (full load 350W with Forced Air)


MPOF350-20B2XX-C Input Voltage Derating Curve






Note: With an AC input voltage between 90 - 100VAC and a DC input between 127 - 140VDC the output power must be derated as per the temperature derating curves.





## **Dimensions and Recommended Layout**



### Notes:

- 1. Unless otherwise specified, parameters in this datasheet were measured under the conditions of Ta=25°C, humidity<75%RH with nominal input voltage and rated output load;
- 3. The ambient temperature derating of 5°C/1000m is needed for operating altitude greater than 2000m;
- 4. All index testing methods in this datasheet are based on our company corporate standards;
- 5. In order to improve the efficiency at light load, there will be audible noise generated, but it does not affect product performance and reliability;
- 6. We can provide product customization service, please contact our technicians directly for specific information;
- 7. Products are related to laws and regulations: see "Features" and "EMC";
- 8. The out case needs to be connected to PE ( ) of system when the terminal equipment in operating;
- 9. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units;
- 10. Warning: Use double fuses, please disconnect the power before maintenance and replacement;
- 11. The power supply is considered a component which will be installed into a final equipment. All EMC tests should be confirmed with the final equipment. Please consult our FAE for EMC test operation instructions.

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

