


TECHNICAL DATA SHEET	code	MRG5902
	version	2
	date	2005-12-12
COAX RG59 LSNH	page	1/2

APPLICATION

Coaxial cables used in cabled distribution networks designed according the European Standard EN 50117 operating at frequencies between 5 MHz and 860 MHz and the International Standard IEC 1196.

CONSTRUCTION



1 Inner conductor Copper clad steel

2 Dielectric Solid PE

3 Braid Annealed copper

4 Sheath LSNH according the European Standard HD 624.

REQUIREMENTS AND TEST METHODS

Test methods in accordance with European standard EN 50117-1.

Mechanical characteristics

1. Inner conductor.

Diameter: $0.58 \text{ mm} \pm 0.02 \text{ mm}$

2. Dielectric:

Diameter: $3.7 \text{ mm} \pm 0.15 \text{ mm}$

3. Outer conductor:

Diameter screen: $4.3 \text{ mm} \pm 0.2 \text{ mm}$

Coverage braid: $91 \% \pm 4 \%$

4. Sheath:

Diameter: $6.15 \text{ mm} \pm 0.2 \text{ mm}$ Tensile strength: $\geq 12.5 \text{ N/mm}^2$ Elongation at break: $\geq 150 \%$

5. Cable:

Crush resistance of cable: < 1% (load of 700N)

Storage/operating temperature: -15° C to $+70^{\circ}$ C

Minimum installation temperature: -5 °C Minimum static bend radius: 35 mm Total weight: 100 g/m



TECHNICAL DATA SHEET	code	MRG5902
	version	2
	date	2005-12-12
COAX RG59 LSNH	page	2/2

Electrical characteristics

Mean characteristic impedance: $75 \pm 3 \Omega$ Regularity of impedance: > 40 dBDC resistance inner conductor: $\leq 79 \Omega/\text{km}$

Capacitance: 67 pF/m \pm 2 pF/m Velocity ratio: nominal 0.66 Insulation resistance: $> 10^4$ M Ω .km

Voltage test of dielectric: 2 kVdc

Return loss at 5-30 MHz: \geq 20 dB*

30-470 MHz: $\geq 20 \text{ dB*}$ 470-862 MHz: $\geq 18 \text{ dB*}$

*Max. 3 peak values 4 dB lower than specified.

39.2 dB/100m

Attenuation at	Nominal		
5 MHz:	2.9 dB/100m	1000 MHz:	42.9 dB/100m
50 MHz:	8.0 dB/100m	1350 MHz:	50.0 dB/100m
100 MHz:	11.6 dB/100m	1600 MHz:	54.5 dB/100m
230 MHz:	18.3 dB/100m	1750 MHz:	57.0 dB/100m
300 MHz:	21.2 dB/100m	2150 MHz:	63.0 dB/100m
400 MHz:	25.0 dB/100m		
470 MHz:	27.5 dB/100m		

Maximum attenuation is 10% higher.

860 MHz:



Belden CDT believes this product to be in compliance with the environmental regulations EU RoHS (Directive 2002/95/EC, 27 January 2003); this is valid for all material produced after the RoHS compliant date for this product.