

## Workplace mats made of polyurethane, ESD design

Textured surface, height 15 mm, flame-retardant

### Application:

For medium to high stress on dry industrial, statically sensitive working surfaces, dissipates static discharges quickly and safely to prevent overvoltage damage on sensitive electronic parts or devices.

### Version:

- Black, closed mat with textured surface made of polyurethane (CFC-free)
- Four all-round-chamfered safety edges, thus no risk of tripping
- Non-slip surface R10 according to DIN 51130
- Fire safety characteristics tested in accordance with DIN 4102/B2
- Electrical resistance from  $10^5$  to  $10^7$  ohms according to DIN EN 61340-5-1
- Weight: 5.5 kg per m<sup>2</sup>
- Special designs and shapes upon request

### Delivery:

Including 4.5 m earthing cable and 10 mm snap fastener for connecting the mat with the earthing cable



<b>Art. no.</b>	<b>50225 672</b>
<b>Surface structure</b>	Burling / closed
<b>Material</b>	Polyurethane
<b>Length</b>	1200 mm
<b>Width</b>	900 mm
<b>Material thickness</b>	15 mm
<b>Mat design</b>	Individual mat
<b>Min. temperature resistance</b>	-40 °C
<b>Max. temperature resistance</b>	80 °C
<b>Suitable for wet areas</b>	No
<b>Antistatic</b>	Yes
<b>Anti-fatigue</b>	Yes
<b>Non-slip</b>	Yes
<b>Compliant with REACH</b>	Yes
<b>Colour</b>	Black
<b>ESD-capable</b>	Yes

### EAN-Code

5013745000810