

## T1 individual test pin

Diameter 9.00-9.99 mm / graduation 0.01 mm

**ORION**<sup>®</sup>

### Application:

For measuring bore hole clearances, bore diameters, angularity of bores etc.



### Execution:

- Ground and lapped
- Hardened 60-64 HRC
- Diameter of 0.300 to 0.999 mm with a length of 40 mm; from diameter 1.000 mm with a length of 70 mm
- from diameter 3.00 mm: One end with 30-45° chamfer; other end deburred with diameter marking on end face
- diameter from 1.5 to 2.999 mm: One end with 30-45° chamfer; other end deburred with diameter marking on outer surface
- diameter from 1.00 to 1.499 mm: One end with 30-45° chamfer; other end deburred without diameter marking
- up to 0.999 mm: both ends deburred, without diameter marking

<b>Art. no.</b>	<b>32481 944</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	32481944
<b>Diameter</b>	9.44 mm
<b>Tolerance class</b>	1
<b>Material</b>	Gauge steel
<b>Length</b>	70 mm
<b>DIN</b>	2269
<b>Calibration Group</b>	AE
<b>Gross Weight</b>	0.031 kg
<b>Product Group</b>	3DA

### EAN

4039247195510