

Sliding-door cabinet housing with solid sheet metal doors, height 1030 and 1950 mm

For fitting with drawers and shelves - custom configuration

Application:

For customised configuration with drawers and shelves, for secure and clearly-visible storage of tools, accessories, files or many other parts.

Execution:

- Housing made of welded sheet steel construction
- Doors edged and reinforced
- Security lock for safe locking of the cabinets
- Rails plugged in to enable rapid conversion
- Grid system: Shelves and drawers adjustable in increments of 30:30 mm
- Additional equipment options with: Drawers with 90 mm and 150 mm front heights , full extension, see no. 50053 600-6 15 (with divider) and 50053 700-7 15 (without divider). Fixed or removable shelves , see no. 50053 620-635 (with divider) and 50053 720-735 (without divider)

Advantage:

- Space-saving sliding doors: ideal for use in confined and narrow spaces



Art. no.	50053 530
Brand	HK
Manufacturer Part Number	50053530
Height	1030 mm
Width	1000 mm
Depth	500 mm
Effective height	920 mm
With partition wall	Yes
With doors	Yes
Door design	Full-sheet panel
Lock type	Cylinder lock
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Gentian blue RAL 5010
Surface	Powder-coated
Gross Weight	44.000 kg
Product Group	501

EAN

4039247469680