

Forklift truck

Carrying capacity 2500 and 3000 kg



Application:

For lifting and carrying loads on pallets or in standardised containers, ideal tool when working on level floors or other surfaces.

Execution:

- With manual drive system
- Made of painted steel
- Particularly quiet rollers made of polyurethane to avoid damaging delicate bases
- Pressure relief valve if maximum capacity is exceeded in order to avoid damage to the hydraulic system
- Frame powder-coated at 250°C for high wear-resistance
- With retracting and extending rollers and improved ergonomic 3D steel drawbar
- With proportional valve as standard for transporting even delicate and fragile goods such as glass or ceramics.



Art. no.	50262 290
Fork roller diameter	82 mm
Turning radius	1367 mm
Material	Steel
Load-carrying capacity	3000 kg
Fork length	1150 mm
Fork arm width	150 mm
Fork, external distance	525 mm
Min. lift height	85 mm
Lift height	200 mm
Fork castor design	Tandem
Castor-wheel diameter	200 mm
Material of steering wheels	Polyurethane
Steering wheel design	With aluminium inner core
With quick-lift function	No
With weighing system	No
Colour	Green Pantone 382
Surface	Powder-coated
Product Group	Prod. Gr. 559

EAN

8018539089177