6.3mm × 32mm Ceramic Fast Blow Fuses


multicomp PRO




Features

- Quick blow (F)
- Ceramic cartridge, nickel plated brass end caps
- Excellent I2T characteristics
- · Welded element for enhanced vibration tolerance
- Break capacity 1000A

Diagram



Dimensions : Millimetres



Part Number Table

	ï
Description	Part Number
500mA Ceramic 6.3mm×32mm fast blow fuse	CF06333CF500/10
1A Ceramic 6.3mm×32mm fast blow fuse	CF06333CF/1/10
2A Ceramic 6.3mm×32mm fast blow fuse	CF06333CF/2/10
3A Ceramic 6.3mm×32mm fast blow fuse	CF06333CF/3/10
5A Ceramic 6.3mm×32mm fast blow fuse	CF06333CF/5/10
10A Ceramic 6.3mm×32mm fast blow fuse	CF06333CF/10/10
12A Ceramic 6.3mm×32mm fast blow fuse	CF06333CF/12/10
15A Ceramic 6.3mm×32mm fast blow fuse	CF06333CF/15/10
20A Ceramic 6.3mm×32mm fast blow fuse	CF06333CF/20/10

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet sheet sheet sheet sheet sheet he Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro



RoHS Compliant

 \Re_{e}^{s} approved (500mA - 15A) e^{s} approved (1A - 15A)