



HBL8115V -- Straight Blade Products, Hospital Grade Valise Plug



2-Pole 3-Wire Grounding, 15A 125V, 5-15P, White Nylon

Product Specifications

<p>Product Type</p>	 <p>Plugs</p>
<p>Body Style</p>	<p>Straight</p>
<p>Standard</p>	<p>NEMA</p>
<p>Amperage</p>	<p>15A</p>
<p>Voltage</p>	<p>125V</p>
<p>Poles and Wires</p>	<p>2 Pole, 3-Wire Grounding</p>
<p>Hospital Grade ?</p>	<p>Yes</p>
<p>Plug/Connector Grade</p>	<p>Valise</p>
<p>Color</p>	 <p>White</p>
<p>NEMA No.</p>	<p>5-15P</p>
<p>Horsepower</p>	<p>0.5</p>
<p>Cord Dia.</p>	<p>.300"-.660" (7.6-16.8)</p>
<p>Type</p>	<p>2 Pole, 3 Wire, Grounding</p>
<p>Rating</p>	<p>15A, 125V</p>
<p>Certification</p>	<p>UL Listed to UL498 File E1706, CSA Certified to C22.2 No. 42 File 280</p>
<p>IP Suitability</p>	<p>IP20</p>
<p>Housing Material</p>	<p>Nylon</p>
<p>Cord Clamp Material</p>	<p>Noryl (Polyphenylene Oxide)</p>
<p>Contact Blades Material</p>	<p>.060" (1.5) Brass</p>

Ground Contact Blade Material	.040" Brass
Terminal Screw Material	Stainless Steel
Ground Screw Material	Stainless Steel (green finish)
Dielectric Voltage	Withstands 2,000V minimum.
Current Interrupting	Certified for current interrupting at full rated current.
Temperature Rise	Max 30°C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of 75%..
Terminal Identification	Terminals identified in accordance with UL498 (Brass, White, Green).
Terminal Accommodation	#18-#12 AWG copper stranded or solid conductor only.
Product Identification	Ratings are a permanent part of the device.
Flammability	UL 94 V2.
Operating Temperatures	Maximum continuous 75°C, minimum -40°C (w/o impact).
Certified	UL2305 OEM and replacement use on convention center flat cable cord sets.
UPC Number	783585015637
Weight in LBs	0.150

