

## Four Indent Crimping Tool SelectorCrimp HDT-48



Art. No. 8782 0009 6



Selector position easily readable on the pliers



Crimp indenter depth setting through an 8 position selector



Supplied with universal locator

## Four Indent Crimping Tool SelectorCrimp HDT-48

- Specialty crimping pliers for processing turned male and female contacts of the DT-series from TE Connectivity (formerly known as Deutsch terminals)
- Crimp quality testing through GO-NOGO gauges (optional)
- Reliable crimping results through forced locking mechanism and synchronous feed setting of indenters
- Optimized opening width, ergonomic design, and reduced hand force





The following table lists all common contacts that can be processed in the four indent crimping tool SelectorCrimp HDT-48.

for contacts							
Contact number	AWG	mm <sup>2</sup>	Contact number	AWG	mm <sup>2</sup>	Contact number	AWG
0460-204-12**	12-14	2.0-3.0 mm <sup>2</sup>	0462-221-16**	20	0.50 mm <sup>2</sup>	M39029/4-110 (TE 0641-1-2031L)	20
0460-220-12**	12-14	2.0-3.0 mm <sup>2</sup>	0460-010-20**	16-18	0.75-1.0 mm <sup>2</sup>	M39029/4-111 (TE 0641-2-1631L)	16
0462-203-12**	12-14	2.0-3.0 mm <sup>2</sup>	0462-005-20**	16-18	0.75-1.0 mm <sup>2</sup>	M39029/4-113 (TE 0641-3-1231L)	12
0462-210-12**	12-14	2.0-3.0 mm <sup>2</sup>	0460-202-20**	20-22	0.35-0.50 mm <sup>2</sup>	M39029/5-115 (TE 100503L)	20
0460-215-16**	14*	2.0 mm <sup>2</sup>	0462-201-20**	20-22	0.35-0.50 mm <sup>2</sup>	M39029/5-116 (TE 100504L)	16
0462-209-16**	14*	2.0 mm <sup>2</sup>	4060-002-12**	12-14	2.0-3.0 mm <sup>2</sup>	M39029/5-118 (TE 100505L)	12
0460-002-16**	16	1.0-1.5 mm <sup>2</sup>	4062-002-12**	12-14	2.0-3.0 mm <sup>2</sup>		
0460-202-16**	16	1.0-1.5 mm <sup>2</sup>	4060-001-16**	16-18	0.75-1.5 mm <sup>2</sup>		
0462-201-16**	18	0.75 mm <sup>2</sup>	4062-001-16**	16-18	0.75-1.5 mm <sup>2</sup>		

\* Use 1.5 mm<sup>2</sup> setting for this part with 14 AWG.

\*\* = 31, plating is Gold. / \*\* = 141, plating is Nickel.

Art. No.	EAN 4049002	Model	Picture	Capacity	max. Ø of contact	↔ mm	⚖ g
8782 0009 6	145704	Crimping tool with universal locator, 2- comp. handle		0.35 – 3.0 mm <sup>2</sup> / AWG 22 – 12	5.5 mm	230	650
8791 7801 01	121456	GO-NOGO pair of Gauges		für Zange 8782 0009 6		76,5	25

Rennsteig Werkzeuge GmbH  
 An der Koppel 1

98587 Steinbach-Hallenberg

T +49 (0) 36847 / 4 41 - 0  
 F +49 (0) 36847 / 4 41 - 14  
 W [www.rennsteig.com](http://www.rennsteig.com)  
 E [info@rennsteig.com](mailto:info@rennsteig.com)

