

Machine tap extension with internal cooling and h6 shank

For the use of machine taps with internal cooling

ORION[®]

Application:

For extending machine taps in conjunction with deep and difficult to reach threads on CNC and conventional machines, in tapping chucks or quick-change chucks in single part production.



Version:

- Steel tool holder with collet chuck and clamping nut h6 shank, steel shank of the extension pursuant to DIN for high requirements for process reliability and service life

Advantage:

- Very flexible and fast solution as there is no need to procure special machine taps
- User-friendly handling and short retooling times
- Excellent value for money

Art. no.	13533 404
Suitable for DIN 374/376 screw tap	M8
Suitable for DIN 371 screw tap	M4.5-M6
Suitable for screw tap square socket size	4.9 mm
Size of square	6.2 mm
Collect depth	26 mm
Collet chuck diameter	6 mm
Collect outer diameter	12.1 mm
Shaft diameter	8 mm
Length	130 mm
Shaft length	60 mm

EAN-Code

4053625475469