

N-ISOL. TERMINAL THERMOPLASTIC SCREW  
 TERMINAL BLUE, 6MM, SZ 2.5




Figure similar

Model		
Busbar design		6x6 mm
General technical data		
Insulation material		thermoplastic
Terminal contact spacing	mm	6
Protection class		
Combustibility class acc. to UL 94		others
Main circuit		
Operating voltage / Rated value	V	500
Operating current / Rated value	A	24
Appearance		
Color		blue
Product details		
Product component / required / connection plate		No
Number		
Number of terminal points		1
Connections		
Connectable conductor cross-section / stranded		
• minimum	mm <sup>2</sup>	2.5
• maximum	mm <sup>2</sup>	2.5
Connectable conductor cross-section		
• solid		

- minimum mm<sup>2</sup> 2.5
- maximum mm<sup>2</sup> 2.5
- finely stranded
  - with core end processing / minimum mm<sup>2</sup> 2.5
  - with core end processing / maximum mm<sup>2</sup> 2.5
  - without core end processing / minimum mm<sup>2</sup> 2.5
  - without core end processing / maximum mm<sup>2</sup> 2.5

<b>Type of electrical connection</b>		screw-type terminals
--------------------------------------	--	----------------------

### Mechanical Design

Height / with lowest-profile installation	mm	35
<b>Length</b>	mm	55
<b>Mounting type</b>		others
Material / of the insulating body		Thermoplast

<b>General Product Approval</b>	<b>Test Certificates</b>	<b>Shipping Approval</b>
---------------------------------	--------------------------	--------------------------



[other](#)



<b>Shipping Approval</b>	<b>other</b>
--------------------------	--------------



[Environmental Confirmations](#)

[other](#)

### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8WA1011NF01>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<http://support.automation.siemens.com/WW/view/en/8WA1011NF01/all>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8WA1011NF01](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8WA1011NF01)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://ausschreibungstexte.siemens.com/tiplv>

**last modified:**

11.03.2015