

1.4kW Single-Phase Metered PDU, 120V Outlets (13 5-15R), 5-15P, 100-127V Input, 15ft Cord, 1U Rack-Mount

MODEL NUMBER: PDUMH15



Highlights

- Metered single phase 15A 120V PDU
- 1U horizontal rackmount, Digital current meter
- NEMA 5-15P input with 15 ft. / 4.5m line cord
- 13 NEMA 5-15R outlets (1 front / 12 rear)
- Reversible housing, 4.5 in. / 11.4 cm depth

Package Includes

- PDUMH15 Metered rackmount PDU
- Owner's manual with warranty information

Description

Tripp Lite Metered PDU / Power Distribution Units offer real-time local reporting of load level in amps via built-in digital meter. Enables visual current monitoring of PDU output current to prevent circuit overloads as additional equipment is added. Offers reliable rackmount multi-outlet power distribution from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Features

- 15A single phase 120V Metered Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- Attached NEMA 5-15P 15A 120V input plug with 15 ft. / 4.5m line cord
- 1U horizontal rackmount format installs in one rack space
- 13 NEMA 5-15R outlets (1 front facing / 12 rear)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
- Back panel grounding lug

Specifications

OVERVIEW	
UPC Code	037332132529



PDU Type	Metered
INPUT	
PDU Input Voltage	100; 120; 127
Recommended Electrical Service	15A 120V
Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A continuous
PDU Plug Type	NEMA 5-15P
Input Phase	Single-Phase
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Capacity Details	1.52kW (127V), 1.44kW (120V), 1.2kW (100V) / 15A total capacity (Agency de-rated to 12A); 12A max per outlet
Output Receptacles	(13) 5-15R
Output Nominal Voltage	100; 120; 127
Overload Protection	15A Breaker
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
Switches	n/a
PHYSICAL	
Form Factors Supported	1U rackmount, 0U vertical rackmount, wall-mount, and under-counter installation
Material of Construction	Metal
Minimum Required Rack Depth (cm)	19.05
Minimum Required Rack Depth (inches)	7.5
Outlets Measurement (Center to Center)	Rear Side = 30.20mm
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / cm)	23.62 x 5.08 x 51.56
Shipping Dimensions (hwd / in.)	9.30 x 2.00 x 20.30
Shipping Weight (kg)	2.40
Shipping Weight (lbs.)	5.30
Unit Dimensions (hwd / cm)	4.45 x 44.45 x 11.43
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 4.5



Unit Weight (kg)	2.04
Unit Weight (lbs.)	4.5
ENVIRONMENTAL	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
SPECIAL FEATURES	
TVSS Grounding	Rear grounding lug
STANDARDS & COMPLIANCE	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>