

Hazardous materials depot

One door, with collection tray and grating, with fixed lid

Application:

For the regulatory-compliant storage of flammable liquids in GHS categories 1-3 and liquids which pose a hazard to water in GHS categories 1-4 both inside and outside.

Version:

- Collecting tray from 3 mm sheet steel
- Galvanised grating (carrying capacity 1000 kg/m²)
- 100 mm ground clearance
- Construction closed on all sides, from zinc-coated, profiled sheet steel
- Natural ventilation
- 1 single-leaf door, lockable
- Filling pumps or filling funnels can be stored together with the drum
- With fixed lid
- With general technical approval



Art. no.	50069 335
Height	2400 mm
Width	1550 mm
Depth	1525 mm
Number of doors	1 PCS
Max. number of 1000-litre containers (IBC)	1 PCS
Collection volume	1000 l
For liquids hazardous to water GHS 1-4	Yes
For flammable liquids GHS 1-3	Yes
Folding roof	No
Load-carrying capacity of grating	1000 kg
Material	Sheet steel
Surface	Lacquered
Colour	Optional