

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0513532400](#)
Status: **Active**
Overview: [MicroClasp Wire-to-Board System](#)
Description: 2.00mm Pitch MicroClasp Wire-to-Board Receptacle Housing, Positive Lock, Dual Row, 24 Circuits, White

Documents:

[3D Model](#) [Packaging Specification SPK-51353-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-51353-003-001 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family Crimp Housings
 Series [51353](#)
 Application Signal, Wire-to-Board
 Overview [MicroClasp Wire-to-Board System](#)
 Product Name MicroClasp
 UPC 756054235836


Physical

Circuits (maximum) 24
 Color - Resin White
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Capable No
 Lock to Mating Part Yes
 Material - Resin Nylon
 Net Weight 1123.600/mg
 Number of Rows 2
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 2.00mm
 Stackable No
 Temperature Range - Operating -25° to +85°C

Material Info

Reference - Drawing Numbers

Packaging Specification SPK-51353-001-001
 Product Specification PS-51353-003-001
 Sales Drawing SD-51353-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[51353](#) Series

Mates With

[55917](#) Vertical Header with Kinked PC Tails,
[55959](#) Right Angle Header, [501844](#) Vertical Header

Use With

[56134](#) Terminal