

Aluminum Electrolytic Capacitors, Power Eurodin, Screw Terminals



LINKS TO ADDITIONAL RESOURCES



Fig. 1

| QUICK REFERENCE DATA | |
|---|-------------------------|
| DESCRIPTION | VALUE |
| Nominal case size (Ø D x L in mm) | 35 x 60 to 90 x 220 |
| Rated capacitance range (E6 series), C _R | 1000 µF to 330 000 µF |
| Tolerance on C _R | -10 % to +30 % |
| Rated voltage range, U _R | 25 V to 100 V |
| Category temperature range | -40 °C to +85 °C |
| Endurance test at 85 °C | 8000 h |
| Useful life at 85 °C | 20 000 h |
| Shelf life at 0 V, 85 °C | 500 h |
| Based on sectional specification | IEC 60384-4 / EN 130300 |
| Climatic category IEC 60068 | 40 / 085 / 56 |

FEATURES

- Very long useful life: 20 000 h at 85 °C
- Extremely low ESR and ESL allowing very high ripple current load
- High resistance to shock and vibration
- Polarized aluminum electrolytic capacitors, non-solid electrolyte
- Large types, cylindrical aluminum case, insulated with a blue sleeve
- Also available in bolt version (106 PED-STB)
- Pressure relief in the sealing
- Charge and discharge proof
- High reliability
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


**RoHS
COMPLIANT**

APPLICATIONS



- Computer, telecommunications, and industrial systems
- Smoothing and filtering
- Standard and switched mode power supplies
- Energy storage in pulse systems

MARKING

The capacitors are marked with the following information:

- Rated capacitance (in µF)
- Tolerance on rated capacitance, code letter in accordance with IEC 60062 (Q for -10 % / +30 %)
- Rated voltage (in V)
- Date code
- Name of manufacturer
- Code for factory of origin
- “-” sign to identify the negative terminal, visible from the top and side of the capacitor
- Code number
- Climatic category in accordance with IEC 60068
- “LL” for long life grade

| SELECTION CHART FOR C _R , U _R , AND RELEVANT NOMINAL CASE SIZES (Ø D x L in mm) | | | | |
|---|--------------------|----------|----------|----------|
| C _R (µF) | U _R (V) | | | |
| | 25 | 40 | 63 | 100 |
| 1000 | - | - | - | 35 x 60 |
| 1500 | - | - | - | 35 x 60 |
| 2200 | - | - | 35 x 60 | 35 x 80 |
| 3300 | - | 35 x 60 | 35 x 60 | 35 x 105 |
| 4700 | 35 x 60 | 35 x 60 | 35 x 80 | 50 x 80 |
| 6800 | 35 x 60 | 35 x 80 | 35 x 105 | 50 x 105 |
| 10 000 | 35 x 80 | 35 x 105 | 50 x 80 | 65 x 105 |
| 15 000 | 35 x 105 | 50 x 80 | 50 x 105 | 65 x 105 |
| 22 000 | 50 x 80 | 50 x 105 | 65 x 105 | 76 x 105 |
| 33 000 | 50 x 105 | 65 x 105 | 65 x 105 | 76 x 146 |
| 47 000 | 65 x 105 | 65 x 105 | 76 x 105 | 76 x 220 |
| 68 000 | 65 x 105 | 76 x 105 | 76 x 146 | 90 x 220 |
| 100 000 | 76 x 105 | 76 x 146 | 76 x 220 | - |
| 150 000 | 76 x 146 | 76 x 220 | - | - |
| | - | 90 x 146 | 90 x 220 | - |
| 220 000 | 76 x 220 | - | - | - |
| | 90 x 146 | 90 x 220 | - | - |
| 330 000 | 90 x 220 | - | - | - |

DIMENSIONS in millimeters AND AVAILABLE FORMS

 Fig. 2A - Mechanical drawings for standard M5 disc versions.
 For details refer to Table 1

 Fig. 2B - Mechanical drawings for high current M6 disc versions.
 For details refer to Table 1

Note

- Maximum permissible torque which may be applied to the termination screws: 2 Nm for M5; 2.5 Nm for M6
 For accessories refer to document "Mounting Accessories", see www.vishay.com/doc?28348
 The capacitors are delivered with screws and washers

Table 1

| DIMENSIONS in millimeters AND MASS | | | | | | | | | | | | | | |
|------------------------------------|---------|-----------|-------------|-----------|-------------|-------------|-------------|-------------|---------------|----|-------|-------|---------------|----------|
| DESIGN | DRAWING | $L \pm 1$ | $L_t \pm 1$ | $D \pm 1$ | $P \pm 0.3$ | $T \pm 0.2$ | $H \pm 0.3$ | $B \pm 0.3$ | $d_1 \pm 0.1$ | M | S - 0 | M_b | $l_b \pm 0.1$ | MASS (g) |
| 35 x 60 | 2A | 63.3 | 68.7 | 35.3 | 12.8 | 7.0 | 4.6 | 11.0 | 7.9 | M5 | 9.5 | M8 | 12.0 | 75 |
| 35 x 80 | 2A | 81.3 | 86.7 | 35.3 | 12.8 | 7.0 | 4.6 | 11.0 | 7.9 | M5 | 9.5 | M8 | 12.0 | 95 |
| 35 x 105 | 2A | 103.3 | 108.7 | 35.3 | 12.8 | 7.0 | 4.6 | 11.0 | 7.9 | M5 | 9.5 | M8 | 12.0 | 130 |
| 50 x 80 | 2A | 82.8 | 88.8 | 51.0 | 22.2 | 7.1 | 4.8 | 11.0 | 7.9 | M5 | 9.5 | M12 | 16.0 | 200 |
| 50 x 105 | 2A | 104.8 | 110.8 | 51.0 | 22.2 | 7.1 | 4.8 | 11.0 | 7.9 | M5 | 9.5 | M12 | 16.0 | 300 |
| 65 x 105 | 2A | 104.8 | 110.7 | 65.0 | 28.5 | 7.0 | 4.6 | 11.9 | 7.9 | M5 | 9.5 | M12 | 16.0 | 480 |
| 65 x 105 HC | 2B | 104.8 | 109.2 | 65.0 | 28.5 | 5.5 | 3.5 | 18.0 | 13.0 | M6 | 8.5 | M12 | 16.0 | 480 |
| 76 x 105 | 2A | 105.8 | 111.7 | 76.4 | 31.8 | 7.0 | 4.6 | 11.7 | 7.9 | M5 | 9.5 | M12 | 16.0 | 700 |
| 76 x 105 HC | 2B | 105.8 | 110.2 | 76.4 | 31.8 | 5.5 | 3.5 | 18.3 | 13.0 | M6 | 8.5 | M12 | 16.0 | 700 |
| 76 x 146 | 2A | 145.8 | 151.7 | 76.4 | 31.8 | 7.0 | 4.6 | 11.7 | 7.9 | M5 | 9.5 | M12 | 16.0 | 1000 |
| 76 x 146 HC | 2B | 145.8 | 150.2 | 76.4 | 31.8 | 5.5 | 3.5 | 18.3 | 13.0 | M6 | 8.5 | M12 | 16.0 | 1000 |
| 76 x 220 | 2A | 219.8 | 225.7 | 76.4 | 31.8 | 7.0 | 4.6 | 11.7 | 7.9 | M5 | 9.5 | M12 | 16.0 | 1500 |
| 76 x 220 HC | 2B | 219.8 | 224.2 | 76.4 | 31.8 | 5.5 | 3.5 | 18.3 | 13.0 | M6 | 8.5 | M12 | 16.0 | 1500 |
| 90 x 146 HC | 2B | 150.1 | 155.4 | 89.4 | 31.8 | 7.9 | 0.0 | 13.0 | 13.0 | M6 | 10.0 | M12 | 16.0 | 1300 |
| 90 x 220 HC | 2B | 218.1 | 223.4 | 89.4 | 31.8 | 7.9 | 0.0 | 13.0 | 13.0 | M6 | 10.0 | M12 | 16.0 | 2000 |



| PACKAGING QUANTITIES AND DIMENSIONS in millimeters | | |
|--|---|---------------------------------|
| DESIGN | PACKAGING QUANTITIES (units per box) | CARDBOX DIMENSIONS L x W x H |
| 35 x 60 | 50 | 377 x 375 x 88 |
| 35 x 80 | 50 | 377 x 375 x 123 |
| 35 x 105 | 50 | 377 x 375 x 129 |
| 50 x 80 | 25 | 377 x 375 x 123 |
| 50 x 105 | 25 | 377 x 375 x 129 |
| 65 x 105 | 16 | 377 x 375 x 129 |
| 65 x 105 HC | 16 | 377 x 375 x 129 |
| 76 x 105 | 12 | 377 x 375 x 129 |
| 76 x 105 HC | 12 | 377 x 375 x 129 |
| 76 x 146 | 12 | 377 x 375 x 168 |
| 76 x 146 HC | 12 | 377 x 375 x 168 |
| 76 x 220 | 12 | 377 x 375 x 242 |
| 76 x 220 HC | 12 | 377 x 375 x 242 |
| 90 x 146 HC | 8 | 377 x 375 x 168 |
| 90 x 220 HC | 8 | 377 x 375 x 242 |

Note

- For STB version holds:
H cardbox box: + 10 mm

| ELECTRICAL DATA | |
|-----------------|---|
| SYMBOL | DESCRIPTION |
| C_R | Rated capacitance at 100 Hz, tolerance -10 % to +30 % |
| I_R | Rated RMS ripple current at 100 Hz, 85 °C |
| I_{L5} | Max. leakage current after 5 min at U_R |
| ESR | Max. equivalent series resistance at 100 Hz |
| Z | Max. impedance at 20 kHz |

ORDERING EXAMPLE

Electrolytic capacitor 106 PED-ST series
 10 000 μ F / 25 V; -10 % / +30 %
 Nominal case size: \varnothing 35 mm x 80 mm, ST version
 Ordering code: MAL210616103E3

Note

- Unless otherwise specified, all electrical values in Tables 2 and 3 apply at $T_{amb} = 20$ °C, P = 86 kPa to 106 kPa, RH = 45 % to 75 %

Table 2

| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | | | | | |
|--|-------------------------------|---|---------------------------------|----------------------------|--|--------------------------------------|--|---|--|---|
| U_R (V) | C_R 100 Hz (μ F) | NOMINAL CASE SIZE \varnothing D x L (mm) | I_R 100 Hz 85 °C (A) | I_{L5} 5 MIN. (mA) | ESR MAX. 100 Hz (m Ω) | Z MAX. 20 kHz (m Ω) | STANDARD M5 DISC | | HIGH CURRENT M6 DISC | |
| | | | | | | | ST ORDERING CODE MAL2106..... | STB ORDERING CODE MAL2106..... | ST ORDERING CODE MAL2106..... | STB ORDERING CODE MAL2106..... |
| 25 | 4700 | 35 x 60 | 5.8 | 0.24 | 70 | 50 | 16472E3 | 56472E3 | - | - |
| | 6800 | 35 x 60 | 6.3 | 0.34 | 55 | 42 | 16682E3 | 56682E3 | - | - |
| | 10 000 | 35 x 80 | 7.7 | 0.50 | 40 | 31 | 16103E3 | 56103E3 | - | - |
| | 15 000 | 35 x 105 | 9.0 | 0.75 | 30 | 24 | 16153E3 | 56153E3 | - | - |
| | 22 000 | 50 x 80 | 13.5 | 1.10 | 19 | 15 | 16223E3 | 56223E3 | - | - |
| | 33 000 | 50 x 105 | 16.0 | 1.65 | 14 | 12 | 16333E3 | 56333E3 | - | - |
| | 47 000 | 65 x 105 | 22.5 | 3.35 | 10 | 10 | 16473E3 | 56473E3 | 36473E3 | 76473E3 |
| | 68 000 | 65 x 105 | 23.0 | 3.40 | 10 | 10 | 16683E3 | 56683E3 | 36683E3 | 76683E3 |
| | 100 000 | 76 x 105 | 29.5 | 5.00 | 9 | 8 | 16104E3 | 56104E3 | 36104E3 | 76104E3 |
| | 150 000 | 76 x 146 | 34.0 | 7.5 | 8 | 8 | 16154E3 | 56154E3 | 36154E3 | 76154E3 |
| | 220 000 | 76 x 220 | 40.0 | 11.0 | 8 | 8 | 16224E3 | 56224E3 | 36224E3 | 76224E3 |
| | 220 000 | 90 x 146 | 50.0 | 11.0 | 8 | 8 | - | - | 46224E3 | 86224E3 |
| | 330 000 | 90 x 220 | 50.0 | 16.5 | 8 | 8 | - | - | 46334E3 | 86334E3 |



| ELECTRICAL DATA AND ORDERING INFORMATION | | | | | | | | | | |
|--|----------------------------------|---|--|-----------------------------------|-------------------------------|-----------------------------|--|---|--|---|
| U _R (V) | C _R 100 Hz (μF) | NOMINAL CASE SIZE Ø D x L (mm) | I _R 100 Hz 85 °C (A) | I _{L5} 5 MIN. (mA) | ESR MAX. 100 Hz (mΩ) | Z MAX. 20 kHz (mΩ) | STANDARD M5 DISC | | HIGH CURRENT M6 DISC | |
| | | | | | | | ST ORDERING CODE MAL2106..... | STB ORDERING CODE MAL2106..... | ST ORDERING CODE MAL2106..... | STB ORDERING CODE MAL2106..... |
| 40 | 3300 | 35 x 60 | 5.5 | 0.27 | 71 | 49 | 17332E3 | 57332E3 | - | - |
| | 4700 | 35 x 60 | 5.8 | 0.38 | 59 | 44 | 17472E3 | 57472E3 | - | - |
| | 6800 | 35 x 80 | 7.1 | 0.55 | 42 | 32 | 17682E3 | 57682E3 | - | - |
| | 10 000 | 35 x 105 | 10.6 | 0.80 | 23 | 16 | 17103E3 | 57103E3 | - | - |
| | 15 000 | 50 x 80 | 12.5 | 1.20 | 20 | 16 | 17153E3 | 57153E3 | - | - |
| | 22 000 | 50 x 105 | 14.5 | 1.76 | 16 | 12 | 17223E3 | 57223E3 | - | - |
| | 33 000 | 65 x 105 | 21.0 | 2.64 | 11 | 8 | 17333E3 | 57333E3 | 37333E3 | 77333E3 |
| | 47 000 | 65 x 105 | 24.5 | 3.76 | 8 | 8 | 17473E3 | 57473E3 | 37473E3 | 77473E3 |
| | 68 000 | 76 x 105 | 27.0 | 5.44 | 8 | 8 | 17683E3 | 57683E3 | 37683E3 | 77683E3 |
| | 100 000 | 76 x 146 | 31.5 | 8.0 | 8 | 8 | 17104E3 | 57104E3 | 37104E3 | 77104E3 |
| | 150 000 | 76 x 220 | 38.0 | 12.0 | 8 | 8 | 17154E3 | 57154E3 | 37154E3 | 77154E3 |
| | 150 000 | 90 x 146 | 50.0 | 12.0 | 8 | 8 | - | - | 47154E3 | 87154E3 |
| 220 000 | 90 x 220 | 50.0 | 17.6 | 8 | 8 | - | - | 47224E3 | 87224E3 | |
| 63 | 2200 | 35 x 60 | 5.4 | 0.28 | 68 | 47 | 18222E3 | 58222E3 | - | - |
| | 3300 | 35 x 60 | 7.2 | 0.42 | 40 | 27 | 18332E3 | 58332E3 | - | - |
| | 4700 | 35 x 80 | 8.8 | 0.60 | 29 | 19 | 18472E3 | 58472E3 | - | - |
| | 6800 | 35 x 105 | 10.6 | 0.86 | 22 | 15 | 18682E3 | 58682E3 | - | - |
| | 10 000 | 50 x 80 | 14.5 | 1.26 | 16 | 11 | 18103E3 | 58103E3 | - | - |
| | 15 000 | 50 x 105 | 17.0 | 1.89 | 12 | 9 | 18153E3 | 58153E3 | - | - |
| | 22 000 | 65 x 105 | 23.5 | 2.78 | 9 | 8 | 18223E3 | 58223E3 | 38223E3 | 78223E3 |
| | 33 000 | 65 x 105 | 23.5 | 4.16 | 8 | 8 | 18333E3 | 58333E3 | 38333E3 | 78333E3 |
| | 47 000 | 76 x 105 | 25.0 | 5.93 | 8 | 8 | 18473E3 | 58473E3 | 38473E3 | 78473E3 |
| | 68 000 | 76 x 146 | 29.5 | 8.6 | 8 | 8 | 18683E3 | 58683E3 | 38683E3 | 78683E3 |
| | 100 000 | 76 x 220 | 36.5 | 12.6 | 8 | 8 | 18104E3 | 58104E3 | 38104E3 | 78104E3 |
| | 150 000 | 90 x 220 | 50.0 | 18.9 | 8 | 8 | - | - | 48154E3 | 88154E3 |
| 100 | 1000 | 35 x 60 | 3.7 | 0.20 | 96 | 48 | 19102E3 | 59102E3 | - | - |
| | 1500 | 35 x 60 | 4.8 | 0.30 | 59 | 27 | 19152E3 | 59152E3 | - | - |
| | 2200 | 35 x 80 | 5.9 | 0.44 | 42 | 20 | 19222E3 | 59222E3 | - | - |
| | 3300 | 35 x 105 | 7.3 | 0.66 | 29 | 15 | 19332E3 | 59332E3 | - | - |
| | 4700 | 50 x 80 | 10.1 | 0.94 | 22 | 12 | 19472E3 | 59472E3 | - | - |
| | 6800 | 50 x 105 | 12.1 | 1.36 | 16 | 9 | 19682E3 | 59682E3 | - | - |
| | 10 000 | 65 x 105 | 16.7 | 2.00 | 11 | 7 | 19103E3 | 59103E3 | 39103E3 | 79103E3 |
| | 15 000 | 65 x 105 | 17.6 | 3.00 | 10 | 6 | 19153E3 | 59153E3 | 39153E3 | 79153E3 |
| | 22 000 | 76 x 105 | 19.5 | 4.40 | 9 | 6 | 19223E3 | 59223E3 | 39223E3 | 79223E3 |
| | 33 000 | 76 x 146 | 23.0 | 6.6 | 8 | 6 | 19333E3 | 59333E3 | 39333E3 | 79333E3 |
| | 47 000 | 76 x 220 | 28.6 | 9.4 | 5 | 5 | 19473E3 | 59473E3 | 39473E3 | 79473E3 |
| | 68 000 | 90 x 220 | 50.0 | 13.6 | 5 | 5 | - | - | 49683E3 | 89683E3 |

| ADDITIONAL ELECTRICAL DATA | | |
|------------------------------------|--------------------------------------|--|
| PARAMETER | CONDITIONS | VALUE |
| Voltage | | |
| Surge voltage | | $U_s = 1.15 \times U_R$ |
| Reverse voltage | | $U_{rev} \leq 1 \text{ V}$ |
| Current | | |
| Leakage current | After 1 min at U_R | $I_{L1} \leq 0.006 C_R \times U_R + 4 \mu\text{F}$ |
| | After 5 min at U_R | $I_{L5} \leq 0.002 C_R \times U_R + 4 \mu\text{F}$ |
| Inductance | | |
| Equivalent series inductance (ESL) | Case $\varnothing D = 35 \text{ mm}$ | Typ. 13 nH |
| | Case $\varnothing D = 50 \text{ mm}$ | Typ. 16 nH |
| | Case $\varnothing D = 65 \text{ mm}$ | Typ. 19 nH ⁽¹⁾ |
| | Case $\varnothing D = 76 \text{ mm}$ | Typ. 20 nH ⁽¹⁾ |
| | Case $\varnothing D = 90 \text{ mm}$ | Typ. 21 nH ⁽¹⁾ |

Note
⁽¹⁾ Low ESL designs available on request

RIPPLE CURRENT AND USEFUL LIFE

Table 3

| ENDURANCE TEST DURATION AND USEFUL LIFE | |
|---|--------------------------|
| ENDURANCE AT 85 °C (h) | USEFUL LIFE AT 85 °C (h) |
| 8000 | 20 000 |

Note

- Multiplier of useful life code: CCC205-05




Fig. 3 - Multiplier of useful life as a function of ambient temperature and ripple current load



Table 4

| MULTIPLIER OF RIPPLE CURRENT (I_R) AS A FUNCTION OF FREQUENCY | | | | | |
|---|------|------|------|------|-------------|
| FREQUENCY (Hz) | | | | | |
| 50 | 100 | 200 | 400 | 1000 | ≥ 2000 |
| I_R MULTIPLIER | | | | | |
| 0.83 | 1.00 | 1.10 | 1.15 | 1.19 | 1.20 |

Table 5

| TEST PROCEDURES AND REQUIREMENTS | | | |
|--|--|---|---|
| TEST | | PROCEDURE (quick reference) | REQUIREMENTS |
| NAME OF TEST | REFERENCE | | |
| Endurance | IEC 60384-4 / EN 130300 subclause 4.13 | $T_{amb} = 85\text{ }^\circ\text{C}$; U_R applied; 8000 h | $\Delta C/C: \pm 15\%$ $\tan \delta \leq 1.3 \times \text{spec. limit}$ $Z \leq 2 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$ |
| Useful life | CECC 30301 subclause 1.8.1 | $T_{amb} = 85\text{ }^\circ\text{C}$; U_R and I_R applied; 20 000 h | $\Delta C/C: \pm 45\%$ $\tan \delta \leq 3 \times \text{spec. limit}$ $Z \leq 3 \times \text{spec. limit}$ $I_{L5} \leq \text{spec. limit}$ no short or open circuit, no visible damage total failure percentage $\leq 1\%$ |
| Shelf life (storage at high temperature) | IEC 60384-4 / EN 130300 subclause 4.17 | $T_{amb} = 85\text{ }^\circ\text{C}$; no voltage applied; 500 h after test: U_R to be applied for 30 min, 24 h to 48 h before measurement | $\Delta C/C: \pm 10\%$ $\tan \delta \leq 1.2 \times \text{spec. limit}$ $I_{L5} \leq 2 \times \text{spec. limit}$ |

Statements about product lifetime are based on calculations and internal testing. They should only be interpreted as estimations. Also due to external factors, the lifetime in the field application may deviate from the calculated lifetime. In general, nothing stated herein shall be construed as a guarantee of durability.



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.