

SIMATIC ET 200AL, AQ 4xU/I, 4xM12, degree of protection IP67



Figure similar

General information	
Product type designation	AQ 4xU/I
HW functional status	E01
Firmware version	V1.0.x
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal configurable/integrated as of version	STEP 7 V14 or higher
• STEP 7 configurable/integrated as of version	V5.5 SP4 Hotfix 7 or higher
• PROFIBUS as of GSD version/GSD revision	GSD as of Revision 5
• PROFINET as of GSD version/GSD revision	GSDML V2.3.1
Supply voltage	
Load voltage 1L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V

- Reverse polarity protection

Yes; Against destruction; actuator power supply outputs applied with reversed polarity

Input current

Current consumption (rated value)	110 mA; without load
from load voltage 1L+ (unswitched voltage)	4 A; Maximum value
from load voltage 2L+, max.	4 A; Maximum value

Actuator supply

Number of outputs	4
Short-circuit protection	Yes; per module, electronic

Output current

<ul style="list-style-type: none"> • Rated value 	Total current 1 A up to 45 °C; 0.5 A up to 55 °C
---	--

Power loss

Power loss, typ.	2.6 W
------------------	-------

Analog outputs

Number of analog outputs	4
Voltage output, short-circuit protection	Yes
Voltage output, short-circuit current, max.	24 mA
Current output, no-load voltage, max.	15 V
Cycle time (all channels) max.	1 ms

Output ranges, voltage

<ul style="list-style-type: none"> • 0 to 10 V 	Yes; 15 bit
<ul style="list-style-type: none"> • 1 V to 5 V 	Yes; 14 bit
<ul style="list-style-type: none"> • -10 V to +10 V 	Yes; 16 bit incl. sign

Output ranges, current

<ul style="list-style-type: none"> • 0 to 20 mA 	Yes; 15 bit
<ul style="list-style-type: none"> • -20 mA to +20 mA 	Yes; 16 bit incl. sign
<ul style="list-style-type: none"> • 4 mA to 20 mA 	Yes; 14 bit

Connection of actuators

<ul style="list-style-type: none"> • for voltage output two-wire connection 	Yes
<ul style="list-style-type: none"> • for voltage output four-wire connection 	Yes
<ul style="list-style-type: none"> • for current output two-wire connection 	Yes
<ul style="list-style-type: none"> • for current output four-wire connection 	Yes

Load impedance (in rated range of output)

<ul style="list-style-type: none"> • with voltage outputs, min. 	1 k Ω
<ul style="list-style-type: none"> • with voltage outputs, capacitive load, max. 	1 μ F
<ul style="list-style-type: none"> • with current outputs, max. 	500 Ω
<ul style="list-style-type: none"> • with current outputs, inductive load, max. 	1 mH

Destruction limits against externally applied voltages and currents

<ul style="list-style-type: none"> • Voltages at the outputs towards MANA 	16 V
--	------

Cable length

<ul style="list-style-type: none"> • shielded, max. 	30 m
--	------

Analog value generation for the outputs

Settling time

- | | |
|-----------------------|------|
| • for resistive load | 1 ms |
| • for capacitive load | 1 ms |
| • for inductive load | 1 ms |

Errors/accuracies

Output ripple (relative to output range, bandwidth 0 to 50 kHz), (+/-)	0.02 %
--	--------

Linearity error (relative to output range), (+/-)	0.1 %
---	-------

Temperature error (relative to output range), (+/-)	0.005 %/K
---	-----------

Crosstalk between the outputs, max.	-70 dB
-------------------------------------	--------

Repeat accuracy in steady state at 25 °C (relative to output range), (+/-)	0.03 %
--	--------

Operational error limit in overall temperature range

- | | |
|--|--------|
| • Voltage, relative to output range, (+/-) | 0.25 % |
| • Current, relative to output range, (+/-) | 0.25 % |

Basic error limit (operational limit at 25 °C)

- | | |
|--|--------|
| • Voltage, relative to output range, (+/-) | 0.15 % |
| • Current, relative to output range, (+/-) | 0.15 % |

Interrupts/diagnostics/status information

Substitute values connectable	Yes; channel by channel, parameterizable
-------------------------------	--

Alarms

- | | |
|--------------------|----------------------|
| • Diagnostic alarm | Yes; Parameterizable |
|--------------------|----------------------|

Diagnostic messages

- | | |
|-----------------|---|
| • Wire-break | Yes; channel-by-channel, only for output type "current" |
| • Short-circuit | Yes; Actuator supply module by module; channel by channel for output type "voltage" |

Diagnostics indication LED

- | | |
|--------------------------|--------------------|
| • Channel status display | Yes; Green LED |
| • for module diagnostics | Yes; Green/red LED |

Potential separation

between the load voltages	Yes
---------------------------	-----

Potential separation channels

- | | |
|--|-----|
| • between the channels | No |
| • between the channels and backplane bus | Yes |
| • between the channels and the power supply of the electronics | No |

Isolation

Isolation tested with	707 V DC (type test)
-----------------------	----------------------

Degree and class of protection

Degree of protection acc. to EN 60529	
---------------------------------------	--

- IP65
- IP67

Yes
Yes

Ambient conditions

Ambient temperature during operation

- min. -25 °C
- max. 55 °C

Connection method

Design of electrical connection for the inputs and outputs M12, 5-pole

Power supply M8, 4-pole

ET-Connection

- ET-Connection M8, 4-pin, shielded

Dimensions

Width 30 mm

Height 159 mm

Depth 40 mm

last modified: 10/13/2017