



Figure similar

COOLING UNIT DOOR OR WALL MOUNTED COOLING CAPACITY 1550 W 230 V AC RAL 7035 400X950X233 MM (WXHxD) INTERBAL CYCLE IP 54 OUTSIDE CYCLE IP 34

Model		
product brand name		SIVACON
Product designation		Cooling device
Design of the control cabinet cooler		Air/air
General technical data		
A-rated sound power level / maximum	dB	65
Operating pressure / maximum permissible	bar	25
Cooling capacity / at L35L35	W	1 550
Temperature		
• of the inner cooling circuit / minimum	°C	20
• of the inner cooling circuit / maximum	°C	46
• of the outer cooling circuit / minimum	°C	20
Electricity		
Starting current	A	18
Main circuit		
Operating voltage		
• with AC / at 50 Hz / Rated value / maximum	V	230
• with AC / at 60 Hz / Rated value / maximum	V	230
Operating current		
• of the fuse link / Rated value	A	10
• for motor / maximum rated value	A	5.3
Product details		
Product component		

- Heating
- Thermostat

No
Yes

Connections

Type of electrical connection Connector, 4-pole

Mechanical Design

Height	mm	950
Width	mm	400
Depth	mm	233
Installation location		Mounting, parti... integration
Material		steel

Certificates

Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

E
E

General Product Approval



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR64235SK15>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR64235SK15/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR64235SK15

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015