

SDUC boring bar, offset, steel, positive, right-hand

For longitudinal and copy turning with DC indexable insert

ATORN[®]

Application

For longitudinal and copy turning with DC indexable insert 55°.

Version

- Precision-made boring bar, **steel**, with internal cooling, offset, type D, attack angle 93.5°, tip angle 55°, clearance angle 7°

Advantage

- Narrow contour optimised for copying-turning work
- Positive body geometry ensures low cutting forces



Art. No.	17847 210
ISO name	A 0810 H SDUC R/L 07
Min. bore diameter	12.5 mm
Shaft diameter	10 mm
Clearance length	22 mm
Length	100 mm
Clamping surface height	9 mm
Programming size	7 mm
Suitable for indexable inserts	DC.. 0702..
Tool design	Right
DIN	8024

EAN-Code

4050293110371