


DO NOT SCALE DRAWING


REVISIONS

ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	DRAWN	08-08-2013	


Body



Assembly



Rivet



Part No.	Hole	Panel Thickness	A
TRFF-006-P4×5B	Ø4.1-4.2	0.3-0.7	Ø4.0
TRFF-006-P4×6B		0.6-1.0	
TRFF-006-P4×7B		1.0-2.0	
TRFF-006-P4×8B		2.0-3.1	
TRFF-006-P4×9B		3.1-4.1	
TRFF-006-P5×6.5B	Ø5.1-5.2	0.8-1.2	Ø5.0
TRFF-006-P5×7.5B		1.3-2.3	

Notes:

- 1. Material: TPR UL94 HB (Body)
PA6 UL94 V2 (Rivet)
- 2. RoHS Compliant;



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MILLIMETERS.
SURFACE FINISH:
TOLERANCES:
L ≤ 4 = ±0.1 4 < L ≤ 15 = ±0.2
15 < L ≤ 50 = ±0.3 50 < L ≤ 100 = ±0.4

NAME	DATE
DRAWN: MARTIN ELLIOTT	08/08/2013
CHK'D:	
APPV'D:	

MATERIAL

SEE NOTES

HEAT TREATMENT

N/A

FINISH

Black

TITLE

SOFT FAST FOOT

CUSTOMER PART NO.

DWG NO.

TRFF-006

A3

PROJECTION



SHEET 1 OF 1

DESIGN RIGHT. TR FASTENINGS LTD, 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED,
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.