




DIN 6315 B



Brida horquilla
Forked clamp tapered
Bride à fourche
Flange de forquilha

Acero C45
Steel C45
Acier C45
Aço C45

Acabado: Epoxi gris
Surface: Grey powder coated
Finition: Peinture epoxy grise
Acabamento: Epóxi cinzento

* Medidas fuera de norma DIN.
** Dimensions outside DIN standard.*
** Dimensions hors norme DIN.*
** Medidas fora da norma DIN.*

Ref.	B	L	M	A	B1	B2	B3	gr.
6315B-7-60	7	60	M6	12	19	6	3	60
6315B-9-80	9	80	M8	15	25	8	4	140
6315B-11-100	11	100	M10	20	31	10	5	300
6315B-14-125	14	125	M12 M14	25	38	12	6	570
6315B-14-160	14	160	M12 M14	25	38	12	6	730
6315B-14-200	14	200	M12 M14	25	38	12	6	910
6315B-18-160	18	160	M16 M18	30	48	15	8	1.080
6315B-18-200	18	200	M16 M18	30	48	15	8	1.360
6315B-18-250	18	250	M16 M18	40	48	15	10	2.250
6315B-22-200	22	200	M20 M22	40	52	15	10	1.800
6315B-22-250	22	250	M20 M22	40	62	20	10	3.000
6315B-22-315	22	315	M20 M22	40	62	20	10	3.850
6315B-22-500	22	500*	M20 M22	50	62	20	10	7.500
6315B-26-200	26	200	M24	40	66	20	10	2.400
6315B-26-250	26	250	M24	40	66	20	10	3.000
6315B-26-315	26	315	M24	40	66	20	10	3.850
6315B-26-500	26	500*	M24	50	66	20	10	7.500
6315B-34-250	34	250	M30	50	74	20	12	3.700
6315B-34-315	34	315	M30	50	74	20	12	4.750
6315B-34-400	34	400	M30	50	74	20	12	6.100
6315B-34-600	34	600*	M30	50	74	20	12	9.200
6315B-34-1000	34	1.000*	M30	60	94	30	12	28.000
6315B-40-400	40*	400*	M36	60	100	30	12	11.000
6315B-40-600	40*	600*	M36	60	100	30	12	16.500
6315B-43-600	43*	600*	M36 M42	80	123	40	12	29.600

