IDEAL **2245**

**Innovative, compact deskside shredder
with EASY-Touch for intuitive operation**

Level P-2   4 mm strip cut
Sheet capacity*: 11-13 I 9-11

Level P-4   3 x 25 mm particle cut
Sheet capacity*: 6-7 I 5-6

**Level P-5**   2 x 15 mm particle cut
Sheet capacity*: 4-5 I 3-4

* A4 paper 70 g/m² I 80 g/m²

Technical specifications

Volume	20 litres (shred bin)
Power	230 V / 50 Hz**
Motor capacity	150 Watt single phase motor

** other voltages available

Dimensions	428 x 345 x 213 mm (H x W x D)
Weight	6.5 kg / 7.5 kg (particle cut)
ID-No.	11224501

GS certificate-No. DP 10031

Product characteristics

Easy-to use deskside shredder for environmentally conscious users. EASY-Touch multifunction switch element for stand-by / stop (off) / reverse with integrated optical signals for the operational status of the shredder. Photo cell controlled automatic start and stop. Automatic reverse and power cut-off. ZERO ENERGY standby mode: complete, automatic disconnection from power supply after 30 minutes. Transparent safety flap in the feed opening as additional safety element. Quiet, powerful and energy-efficient single phase motor. Double motor protection. High-quality, paper clip proof cutting shafts from special hardened steel with lifetime guarantee. Attractive shred bin from impact-resistant plastic. Practical handle for lifting off the shredder unit from the bin. Magnetic switch for automatic stop if the shredder unit is removed from the shred bin (2245 CC).

IDEAL

IDEAL **2245**

Features

SOLID STEEL CUTTING SHAFTS

Robust and durable: high-quality paper clip proof cutting shafts with lifetime guarantee under conditions of fair wear and tear.

SAFETY FLAP

The safety flap in the feed opening is an additional safety element to keep fingers, ties or other objects away from the cutting shafts.

EASY-TOUCH MULTIFUNCTION SWITCH

Easy operation is guaranteed with the EASY-Touch multifunction switch for stand-by / stop (off) / reverse and optical signals for the operational status of the shredder.

PRACTICAL HANDLE

A practical handle is integrated into the design for lifting off the shredder unit from the shred bin when full.

DGUV Test
Prüf- und Zertifizierungsstelle
Druck und Papierverarbeitung
Fachbereich Energie Textil
Elektro Medienerzeugnisse

<u>Translation</u>   In any case, the German original shall prevail.

GS Certificate

Name and address of the holder of the certificate: (customer)	Krug & Priester GmbH & Co. KG Simon-Schweitzer-Straße 34 72336 Balingen
Product designation:	**file shredder**
Type:	11221002, 11223002, 11224501, 11227001
Testing based on:	DIN EN 60950-1:2014 Information Technology Equipment – Safety – Part 1: General requirements EN 60950-1:2006+A11:2009+A1:2010+A12:2011 Information Technology Equipment – Safety – Part 1: General requirements IEC 60950-1:2005+AMD1:2009+AMD 2:2013 Information Technology Equipment – Safety – Part 1: General requirements EN 1010-1:2004+A1:2010 Safety of machinery – Safety requirements for the design and construction of printing and paper converting machines; Part 1: common requirements
Test report:	612.17 - So/Ho A 14198 Produktgruppe: 001.1001
Further details:	

The type tested meets the requirements specified in article 21 para. 1 of the German Product Safety Act. The holder of the certificate is entitled to affix the GS mark shown overleaf to the products complying with the type tested. At that, the holder of the certificate shall observe the conditions specified overleaf.
The present certificate including the right to affix the GS mark is valid until: **2020-03-24**

Further provisions concerning the validity, the extension of the validity and other conditions are laid down in the Rules of Procedure for Testing and Certification.

Dipl.-Ing. Andreas Vogl

DAkkS
Deutsche
Akkreditierungsstelle
D-ZE-17009-06-01